



Samarium Cobalt Shallow Pot Magnets

For holding and clamping applications

- ▶ 200°C maximum operating temperature
- ▶ Excellent resistance to corrosion
- ▶ Mild steel pot with zinc plated body
- ▶ Ideal for press fit applications



Model Variations

Product Number	Diameter (mm)	Thickness (mm)	Weight (g)	Pull force (kg)	Units per pack
E760	6	4.5	1	0.5	20
E761	8	4.5	1.5	1.1	20
E762	10	4.5	2.5	2.0	20
E763	13	4.5	4.5	4	20
E764	16	4.5	6.5	6	20
E765	20	6	15	9.0	10
E766	25	7	22	15	10
E767	32	7	40	22	10