

In-ear	O			
RF				

Technical drawing of a mechanical assembly, showing a cross-section and a top view.

Top View:

- Outer diameter: 5.6 ± 0.3

Section View:

- Overall length: 18.23 (in parentheses)
- Length of main body: 17.46 (in parentheses)
- Length of bottom section: 4.05 (in parentheses)
- Bottom section length: 6 ± 0.3
- Top diameter: $\phi 6.35 \pm 0.3$
- Inner diameter of top section: $\phi 4.2 \pm 0.2$
- Inner diameter of middle section: $\phi 4.6 \pm 0.2$
- Labels for components:
 - 7
 - 5
 - 8 PRESS FITTING
 - 6
 - 4 PRESS FITTING
 - 2 PRESS FITTING
 - 1
 - 3 PRESS FITTING
 - PRICK PUNCH
 - 1/4-36UNS-2A
- Material: HRM (SMA)
- Feature: E.F.L.

Watermark: HRS DRAWING FOR REFERENCE

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
RoHS COMPLIANT	R.KIMURA	R.KIMURA	M. Yamane	J. Mitani	
	05.08.11	05.08.11	05.08.23	05.08.26	

FORM NO. 228