



4-Port USB 3.0 Type-C Hub

USB-C Male to Four USB-A Females, 5 Gbps SuperSpeed USB (USB 3.2 Gen 1), Bus Powered, Black

SKU: 164924 | EAN-13: 0766623164924 | UPC: 766623164924

More ways to connect your USB-A devices

The Manhattan 4-Port USB 3.0 Type-C Hub turns one of your device's USB-C ports into four SuperSpeed USB-A ports so you can easily connect a keyboard, mouse, thumb drive and more. The hub's SuperSpeed ports are backward compatible so you can bridge older USB-A peripherals to your newer USB-C device. Devices that fit the SuperSpeed USB 3.2 Gen 1 spec (formerly known as USB 3.0) can reach transfer speeds up to 5 Gbps for external storage, printing and more. Plus, you can charge your phone or tablet since the hub supplies up to 5 V / 1 A of power.

Connectivity you can take with you

This hub's durable case, compact size and bus power mean greater portability for you when you have to pack up and go. Simply unplug the hub from your upstream device, disconnect your peripherals and put the devices you need in your laptop bag. Its Plug-and-Play installation and hot-swap ability means you're able to get working — or playing— in no time.

Features:

- Adds four SuperSpeed USB-A ports to a USB-C device to connect a keyboard, mouse, smartphone, tablet and more
- Supports SuperSpeed data transmission up to 5 Gbps
- Bus powered; no external power supply needed
- Includes an LED power indicator
- Plug-and-Play installation; hot swappable
- Windows and Mac compatible
- Three-year warranty

Specifications:

Standards and Certifications

- USB 3.2 Gen 1 (USB 3.0)
- FCC
- CE
- RoHS
- REACH
- UKCA

General

- Data transfer speeds: 5 Gbps
- One USB-C male
- Four USB-A female
- Up to 1 A total power output
- Bus powered

Connections

- One USB-C, 24-pin, male
- Four USB-A, 4-pin, female

Physical

- 24-AWG cable gauge
- Cable length (including connector): 13.5 cm (5.31 in.)
- Withstanding voltage: 300 VDC
- Insulation resistance: 10 MOhm
- Conductive resistance: 5 Ohm
- Housing: ABS plastic
- Dimensions: 107 x 30 x 11 mm (4.21 x 1.18 x 0.43 in.)
- Weight: 39 g (1.1 oz.)

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Shielded

Operating Environment

- Operation Temperature: 0 – 40°C (32 – 104°F)
- Storage Temperature: -20 – 60°C (-4 – 140°F)
- Humidity (noncondensing): 5 – 90%

System Requirements

- Windows XP/Vista/7/8.1/10/11 or Linux or Mac 9.x/10.x or above

Package Contents

- 4-Port USB 3.0 Type-C Hub
- Quick Instruction Guide



