



Bud Industries, Inc.

*ENCLOSURES RIGHT NOW, RIGHT PRICE*

**Model # PTR-28494**



- All plastic construction
- Plastic locking latch and hinges
- Low-cost quality enclosure series designed to perform well in indoor conditions
- Optional steel or plastic internal panel (PTX-18494, PTX-18494-P)
- Body made of gray ABS plastic
- Cover made of gray ABS plastic
- High impact resistance
- IP-67 certified TUV rating to keep out dust and water in extreme conditions
- Meets NEMA type 4X and type 6P (No UL certification)
- ROHS compliant

- UL-94 HB flammability rating
- -20 C to +65 C extended exposure condition
- Continuous poured-in-place neoprene foam gasket

**Specification:**

External Size L x W x D: 15.70" x 19.70" x 6.30"

Internal Size L x W x D: 15.45" x 19.45" x 6.05"

Weight: 2.79 lbs

Color: Light Gray

RoHS Certified: Always Compliant

NEMA Rating: NEMA 4, NEMA 4X, NEMA 6, NEMA 6P

IP Rating: IP67

Features: All Plastic Construction

Mounting Style: Mounting Brackets

Cover Style: Opaque, Hinged Cover

Latch Style: Plastic

Gasket Type: RAKU-PUR® Foam Gasket

Knockouts: No Knockouts

Indoor / Outdoor: Indoor (Not UV Stabilized)

Flammability Rating: UL94-HB

Door Flammability Rating: UL94-HB

Type of Plastic: ABS

Door Type of Plastic: ABS

Service Temperature Min: -20°C

Service Temperature Max: 65°C

Hinge Location: Long Side

If you're looking for a ABS NEMA rated or IP rated enclosure for a printed circuit board (PCB) that measures up to 15.45" x 19.45" x 6.05" or smaller, then this enclosure is an excellent choice.

