

A	1		2		3		4		5	
					Deutsch		English			
					Neindruckbereich		FS-Pressure Range		0 bar ... 600 bar	
					Druckart		Pressure Type		Sealed Reference	
					Art des Ausgangssignales		Type of Output Signal		ratiometrisch/ ratiometric	
					Ausgangsspannung bei Nenndruck		Full-scale Output at Nominal Pressure		4,5 V	
					Nulldrucksignal (Offset)		Zero Pressure Output (Offset)		0,5 V	
					Gesamtfehler/ Druck -40°C ... 0°C 0°C ... +85°C		Total Accuracy/ Pressure -40°C ... 0°C 0°C ... +85°C		max. ± 2,0% FS max. ± 1,0% FS	
					Versorgungsspannung		Supply Voltage		5 V ± 0,25 V	
					Stromaufnahme		Current Consumption		< 20 mA	
B										
C										
D										

Verwendungsbereich Application				Tolerierung/ Tolerances		Maßstab Scale		Gewicht Weight	
803144 Freigegeben		Maße/ Dim. mm		ISO 14405 - (E) DIN ISO 2768-mK		2:1		0,072 kg	
				Name		Dat.		Name	
				Gepr.		16.06.20		Frost	
				Check		16.06.20		Zacharias	