



45° Angled Wire Cap for Cat 6A Shielded TG Jack

CJSUDCAPBU-X

Shielded TG wire cap, Cat. 6, 10 pk., blue0

Specifications

Product Type	Wire Cap
Performance Level	Category 6A
Connector Type	Jack Module - 45° Angled Up/Down
Termination Style	TG Style
Body Material	Die Cast
Module Type	Mini-Com®
Wiring Scheme	T568A/T568B
Shield Type	Shielded (STP)
Sub Brand	Pan-Net®
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Color	Blue

Packaging Detail

UPC	61305657853
Std. Pkg. Qty.	10
Std. Pkg. Volume (cf)	0.0077
Std. Ctn. Qty.	100
Std. Ctn. Volume (cf)	0.0771