



## 45° Angled Wire Cap for Cat 6 Shielded TG Jack

CJSUDCAPIW-X

Shielded TG wire cap, Cat. 6, 10 pk., off white

### Specifications

|                                    |                                  |
|------------------------------------|----------------------------------|
| Product Type                       | Wire Cap                         |
| Performance Level                  | Category 6                       |
| Connector Type                     | Jack Module - 45° Angled Up/Down |
| Termination Style                  | TG Style                         |
| Body Material                      | Die Cast                         |
| Module Type                        | Mini-Com®                        |
| Wiring Scheme                      | T568A/T568B                      |
| Shield Type                        | Shielded (STP)                   |
| Sub Brand                          | Pan-Net®                         |
| Maximum Operating Temperature (°C) | 65                               |
| Maximum Operating Temperature (°F) | 149                              |
| Minimum Operating Temperature (°C) | -10                              |
| Minimum Operating Temperature (°F) | 14                               |
| Color                              | Off White                        |

### Packaging Detail

|                       |             |
|-----------------------|-------------|
| UPC                   | 61305657852 |
| Std. Pkg. Qty.        | 10          |
| Std. Pkg. Volume (cf) | 0.0077      |
| Std. Ctn. Qty.        | 100         |
| Std. Ctn. Volume (cf) | 0.0771      |