

RB53

home » enclosures » rb-series » rb53

Product Image

Size: 4.72" X 3.15" X 2.17"
120mm X 80mm X 55mm

RB53-1TC1BG
Clear top, Gray bottom

RB53-1TG1BG
Gray top, Gray bottom

RB53-1TC1BB
Clear top, Black bottom

RB53-1TB1BB
Black top, Black bottom

RB53-1TC1BC
Clear top, Clear bottom

(4) #4-40 captive Torx SS screws

Watertight case Meets or exceeds NEMA4 and or IP67

(4) #10 X 1/4" HL Pan steel screw (for mounting plate*)

(4) #4-40 Threaded insert (metal)

(6) Mounting plate bosses

Wall mounting holes at corners for #6 screws*

Material: ☀️ UV stabilized Polycarbonate
Flammability rating UL 94 V-0

* not supplied

PARTS INCLUDED		
P/N	Qty.	Description
RB53-1	1	RB53 Top1
RB531	1	RB53 Bottom1
8053	1	RB53 O-ring
6023	4	#4-40 Captive Torx screw
6022	4	#10 X 1/4" HL pan screw
6102	4	#4-40 Threaded insert

5 different Top / Bottom color combinations available

Model	Length	Width	Height	Drawing
RB53	4.72 in	3.15 in	2.17 in	 

 Watch us on YouTube



©2011 Serpac Electronic Enclosures, 2009 Wright Ave., La Verne, CA 91750