

| PLUG                                                      |  | RECEPTACLE                                                |  | RECEPTACLE: MD 021 RS M2 45<br>XX XXX XX XX XX |  |  |  |  |  |
|-----------------------------------------------------------|--|-----------------------------------------------------------|--|------------------------------------------------|--|--|--|--|--|
| <b>SERIES</b>                                             |  |                                                           |  |                                                |  |  |  |  |  |
| MD .050" Rugged Metal Dust Cover                          |  | MD .050" Rugged Metal Dust Cover                          |  |                                                |  |  |  |  |  |
| <b>SIZE</b>                                               |  |                                                           |  |                                                |  |  |  |  |  |
| XXX 009, 015, 021, 025, 031, 037, 051, 069, 100           |  | XXX 009, 015, 021, 025, 031, 037, 051, 069, 100           |  |                                                |  |  |  |  |  |
| <b>STYLE</b>                                              |  |                                                           |  |                                                |  |  |  |  |  |
| RP Plug, rugged metal                                     |  | RS Receptacle, rugged metal                               |  |                                                |  |  |  |  |  |
| <b>PLATING</b>                                            |  |                                                           |  |                                                |  |  |  |  |  |
| M2 Electroless nickel                                     |  | M2 Electroless nickel                                     |  |                                                |  |  |  |  |  |
| M3 Electrodeposited cadmium ☒                             |  | M3 Electrodeposited cadmium ☒                             |  |                                                |  |  |  |  |  |
| M4 Hard anodized black                                    |  | M4 Hard anodized black                                    |  |                                                |  |  |  |  |  |
| <b>HARDWARE</b>                                           |  |                                                           |  |                                                |  |  |  |  |  |
| STYLE OF HARDWARE:                                        |  | STYLE OF HARDWARE:                                        |  |                                                |  |  |  |  |  |
| 22 Two integrated jacknuts (62")                          |  | 22 Two integrated jacknuts (62")                          |  |                                                |  |  |  |  |  |
| 45 Two turning jackscrews, allen head, captivated** (85") |  | 45 Two turning jackscrews, allen head, captivated** (85") |  |                                                |  |  |  |  |  |

\* = Use number in parenthesis when ordering size 100.  
 \*\* = Captive hardware is factory installed and non-removable.  
 Not for use with rear panel mount connectors  
 Not for use on receptacles with grounding fingers  
 ☒ = Option not RoHS compliant