

US POWER SUPPLY 9W







SOFTWARE

RATED VALUE

ABSOLUTE MAXIMUM

Input voltage	100-240 VAC	90-264 VAC
Input Frequency	50/60 Hz	47-63 Hz
Input Current (@100-240 VAC)	0.4 A	-
Inrush Current (@100-240 VAC)	-	40 A
Output Voltage	9 VDC	8.55-9.45 VDC
Output Current	0-1 A	-
Overshoot	5 %	10 %
Certification	UL 60950-1; CSA C22.2 No. 60950-1-07; 47 CFR FCC part 15 subpart B, 10-1-2016; ANSI C63.4:2014; IEC 62321-7-1:2015, IEC 62321-6:2015, IEC 62321-5:2013, IEC 62321-4:2013, IEC 62321:2008 Annex C.	
Short-Circuit protection	v	
Input protection	Fuse	
HIPOT (Dielectric Withstand Test)	Primary to Secondary: 3000 VAC	
MTBF	50000 h	
Input connector	US	
Output connector	4-pin, 3 mm pitch	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Teltonika:](#)

[PR3PUUS3](#)