



## PLT.7M-C Premium Cable Tie

PLT.7M-C

Pan-Ty® locking tie, miniature cross section, 3.1 (79mm) length, nylon 6.6, natural, standard package.

### Specifications

Material Description	Nylon 6.6
Product Type	Premium Cable Tie
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Overall Length (In.)	3.1
Overall Length (mm)	79
Body Width (In.)	0.09
Body Width (mm)	2.3
Body Thickness (In.)	0.032
Body Thickness (mm)	0.8
Maximum Bundle Diameter (In.)	0.68
Maximum Bundle Diameter (mm)	17.3
Minimum Bundle Diameter (In.)	0.03
Minimum Bundle Diameter (mm)	0.8
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant
Military Cross Reference Number	MS3367-4-9
For Use With	GTS-E, GS2B-E, PTS, PPTS, STS2
Application	General
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.

**Packaging Detail**

UPC	07498354771
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0182
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.1824