



**Notes**

Note Compatible with WAGO Edge Computer (hardware: ≥ HW02; software: FW04 (Debian Linux)) and expansion housing for WAGO Edge Computer; Item No. 758-9400 with 1 slot and Item No. 758-9800 with 2 slots

**General technical data**

Slot for Expansion Module	mPCIe
Approvals	CE FCC class A
Connection technology	2 x RJ-45
Supply voltage	3.3 V; at 9 W; typ.

### Communication

Transmission modes	Intel® I350-AM2 LAN Controller
Communication standards	IEEE 1588
Transmission rate	10/100/1000 Mbit/s

### Protection and safety

Protection	Electrostatic Discharge (ESD): 4 KV (contact), 8 KV (air); Electrical Fast Transient (EFT/ Burst): 1000 V
------------	---

### Software

Other system requirements	CAN bus driver ≥ FW04 (Debian Linux)
---------------------------	--------------------------------------

### Material data

Fire load	0 MJ
Weight	150 g

### Environmental requirements

Ambient temperature (operation)	0 ... +60 °C
Ambient temperature (storage)	-40 ... +80 °C
Relative humidity	5 ... 95 % (without condensation)

### Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	TW
GTIN	4066966610284
Customs tariff number	84733020000

### Product Classification

UNSPSC	43222628
ETIM 9.0	EC002584
ETIM 10.0	EC002584
ECCN	NO US CLASSIFICATION

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product  
Compliance 758-9013

