


CLIFF

SLIM Ø3.5mm 4 POLE JACK FRONT MOUNTING FEEDTHROUGH CONNECTOR



Part No.

CP30664

SLIM FM Ø3.5mm 4 Pole Jack Black plastic frame, CSK holes

CP30664X

SLIM FM Ø3.5mm 4 Pole Jack Black plastic frame, Ø2.5 PLAIN holes

CP30664X1

SLIM FM Ø3.5mm 4 Pole Jack Black plastic frame, Ø3.2 PLAIN holes

Feedthrough Features

- Fits standard rectangular cutout.
- Various hole mounting options.
- No soldering or punch termination. Use standard cable for each connector style.
- Low rear profile.

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

Material:

1. Inner Frame: ABS UL94-V2
2. Plastic Frame: PA66 UL94-V2
3. Jack Body: PA9T UL94-V0
4. Jack Shell: SUS301, Nickel plated
5. Contacts: Copper Alloy, Tin plated
6. PCB: FR4

Specification

1. Rating : 0.5A 30V DC
2. Contact Resistance : $\leq 30\text{m}\Omega$
3. Insulation Resistance : $\geq 100\text{M}\Omega$ (DC 250V)
4. Withstand Voltage : 500VAC
5. Operating Temperature : -30°C to 80°C
6. Life Expectancy : 5000+ cycles