

## Product Information

# 82 02 150

### KNIPEX TwinGrip

Front and side gripping pliers



- Gripping, tightening and loosening screws with worn heads and drives
- Unique combination: front and side gripping function, box joint, push-button adjustment
- Biting front jaw with robust teeth and high transmission ratio at the tip of the jaw
- Very slim pliers: Work even in confined spaces, with a narrow turning zone for fast screwing.
- Pinch guard prevents operators' fingers being pinched
- Durable and resilient thanks to robust, box-type pliers joint
- Small and handy – also suitable for more delicate work
- Large front and side gripping capacities: for diameters and width across flats 3 – 16 mm
- Reliable, frontal gripping of flat workpieces up to 6 mm thanks to three-point system
- Three-way adjustable slip joint with push button adjustment for precise alteration of gripping capacity



#### General

Part No.	82 02 150
EAN	4003773089360
Pliers	grey atramentized
Head	polished
Handles	with comfort handles
Weight	278 g
Dimensions	150 x 45 x 18 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

#### Technical details

Adjustment positions	3
Capacities for pipes (diameter)	Ø 0 1/8 - 0 5/8 Inch
Capacities for pipes (diameter)	Ø 3 - 16 mm
Capacities for nuts	3 - 16 mm
Capacities for nuts	0 1/8 - 0 5/8 Inch

Technical changes and errors excepted



