



Cyclops Micro

High Definition Digital Microscope



Exceptional Magnification

Inspect and analyze with ease directly from your HD monitor. Aven's Cyclops Micro Digital Microscope combines ease of use with crystal-clear, superior optics. This system utilizes a macro zoom lens, providing **29x – 185x** magnification, based on a 24" monitor. Designed with the operator in mind, the Cyclops Micro offers a sophisticated high magnification solution while allowing users to remain in a comfortable posture without the need to repeatedly look through narrow microscope eyepieces.

Features

- **1080p resolution**
- **Up to 185x magnification on a 24" monitor**
- **Heavy-duty stand with fine-focus adjustment**
- **Full featured on-screen menu system**
- **Auto/manual focus**
- **Ideal for inspecting small components, SMT PCBs, solder points, and more**

Cyclops Micro Digital Microscope with Micro Lens	
Image Sensor	2MP CMOS
Video Format	1080p @ 60 Frames Per Second
Magnification	29x - 185x
LED Lighting	Ring light with 60 LEDs and brightness controller
Signal Output	1080p HDMI
Gain Control	Automatic/Manual
Digital Magnification	Controlled by included IR remote
Power Supply	DC 5V/2A
Stand	16" post stand with fine focus adjustment
LED Type	Ring light with 60 adjustable LEDs
Field Of View	18.3mm - 2.8mm
Package Contents	Cyclops Digital Microscope Micro Zoom Lens 60 LED ring light with controller Adjustable Stand Manual Power Adapter IR Remote

Part #	Description	
26700-421	Cyclops Micro Digital Microscope	