

FS-100-025

3/4" Plastic Flow Switch 0.25 GPM
Switch Point

 4.0 (4)



Click and hold to
zoom

Choose a Variant

Volumetric Flow Rate, Max: 0.25 GPM

0.25 GPM

0.5 GPM

1 GPM

2 GPM

2.5 GPM

See More

See All Models

See Specs

Product Specs

<< See all Product Models

Brand	
Accuracy	± 10 %
Cable Length	12 in
GrossWeightValue	0.18
Materials	Polypropylene
Media Compatibility	Liquids
Operating Pressure, Max	120 psi
Process Connection Size	3/4 in
Process Connection Type	NPT Female
Process Temperature, Max	80 °C

Process Temperature, Min	0 °C
Series ID	FS-100-Series
Switch Rating	50 VA
Switch Rating Note	Pilot Duty 50 VA, 120 to 240 Vac, 24 to 200 Vdc
Switch Type	SPST NO
Volumetric Flow Rate, Max	0.25 GPM
Volumetric Flow Rate, Min	0 GPM
Country of Origin	China
Show Less	-

Are these specs helpful?  
