



## **Pan-Term® BSN14-3K Butt Splice, Blue, Nylon, 14-18 AWG, PK3000**

**BSN14-3K**

Panduit BSN14-3K Nylon Insulated Butt Splice

### **Specifications**

Product Type	Butt Splice
Base Material	Copper
Barrel Type	Funnel Entry
Finish/Coating	Tin-Plated
Copper Conductor Size	18-14 AWG
Maximum Metric Conductor Size (mm <sup>2</sup> )	2.5
Minimum Metric Conductor Size (mm <sup>2</sup> )	1
Maximum Wire Insulation Diameter (In.)	0.17
Maximum Wire Insulation Diameter (mm)	4.32
Insulation Material	Nylon
Overall Length (In.)	0.95
Overall Length (mm)	24.1
Overall Width (In.)	0.24
Overall Width (mm)	6
Standards Met	UL 486C, CSA C22.2 No.65
UL Temperature Rating (°C)	125
UL Temperature Rating (°F)	257
CSA Temperature Rating (°C)	125
CSA Temperature Rating (°F)	257
Maximum Voltage (V)	600
Maximum Voltage (kV)	0.6
Color Code	Blue
Wire Strip Length (In.)	5/16
Wire Strip Length (mm)	7.9
For Use With	CT-100A, CT-160, CT-260, CT-400, CT460, CT-1550, CT-1551, CT2500, CT500CH
Sub Brand	Reel Smart™

**Specifications (continued)**

Part Features	<ul style="list-style-type: none"><li>• Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time</li><li>• Designed to splice two solid or stranded wires together to repair or lengthen wires</li><li>• Butted configuration provides low profile for limited space applications</li><li>• Internal wire stop assures proper length of insertion into terminal barrel</li></ul>
---------------	---

**Packaging Detail**

UPC	07498383017
Std. Pkg. Qty.	3000
Std. Pkg. Volume (cf)	0.9208
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000