



## **Pan-Term® BSN14-M Butt Splice, Blue, Nylon, 14-16 AWG, PK1000**

**BSN14-M**

Panduit BSN14-M Nylon Insulated Butt Splice

### **Specifications**

|  |   |
|--|---|
| Product Type                                     | Butt Splice   |
| Base Material                                    | Copper  |
| Barrel Type                                      | Standard  |
| Finish/Coating                                   | Tin-Plated  |
| Copper Conductor Size                            | 16-14 AWG   |
| Maximum Metric Conductor Size (mm <sup>2</sup> ) | 2.5   |
| Minimum Metric Conductor Size (mm <sup>2</sup> ) | 1.5   |
| Insulation Material                              | Nylon   |
| Overall Length (In.)                             | 1.15  |
| Overall Length (mm)                              | 29.2  |
| Overall Width (In.)                              | 0.2   |
| Overall Width (mm)                               | 5.1   |
| Standards Met                                    | UL 486C, CSA C22.2 No.65  |
| UL Temperature Rating (°C)                       | 150   |
| UL Temperature Rating (°F)                       | 221   |
| CSA Temperature Rating (°C)                      | 150   |
| CSA Temperature Rating (°F)                      | 221   |
| Maximum Voltage (V)                              | 600   |
| Maximum Voltage (kV)                             | 0.6   |
| Color Code                                       | Blue  |
| Wire Strip Length (In.)                          | 9/32  |
| Wire Strip Length (mm)                           | 7.1   |
| For Use With                                     | CT-100A, CT-160, CT-260, CT-400, CT460, CT-1550, CT-1551, CT2500, CT500CH   |
| Sub Brand  | Pan-Term®   |
| Part Features                                    | <ul style="list-style-type: none"> <li>• Designed to splice two solid or stranded wires together to repair or lengthen wires</li> <li>• Butted configuration provides low profile for limited space applications</li> <li>• Internal wire stop assures proper length of insertion into terminal barrel</li> </ul> |

**Packaging Detail**

|                       |             |
|-----------------------|-------------|
| UPC                   | 07498383003 |
| Std. Pkg. Qty.        | 1000        |
| Std. Pkg. Volume (cf) | 0.5261      |
| Std. Ctn. Qty.        | 0           |
| Std. Ctn. Volume (cf) | 0.0000      |