

DIN Power shell housing for type D



Image is for illustration purposes only. Please refer to product description.

Part number	09 04 032 0502
Specification	DIN Power shell housing for type D
HARTING eCatalogue	https://harting.com/09040320502

Identification

Category	Accessories
Series	DIN 41612
Identification	Data Type D
Type of accessory	Shell housing
Description of the accessory	for female connectors

Version

Version	Top/side entry
Number of cable entries	3
Cable entry	3x
Strain relief	With cable clamps
Locking type	Locking screw
2 parts	Yes
Separable	Yes

Technical characteristics

Limiting temperature	-40 ... +120 °C
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (accessories)	Thermoplastic
Colour (accessories)	RAL 7035 (light grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-2
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	48 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140488656
eCl@ss	27440292 Connector component (accessories)