

Han-Modular Flexbox HBM



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 004 8301
Specification	Han-Modular Flexbox HBM
HARTING eCatalogue	https://harting.com/09140048301

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular® Flexbox
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	for 4 modules a ... d

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP54

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
--------------------------------------	-----

California Proposition 65 substances	Nickel
--------------------------------------	--------

Specifications and approvals

Specifications	IEC 61984
	EN 45545-1
	EN 45545-2

Commercial data

Packaging size	1
----------------	---

Country of origin	Romania
-------------------	---------

European customs tariff number	85389099
--------------------------------	----------

GTIN	5713140354692
------	---------------

eCl@ss	27440202 Shell for industrial connectors
--------	--