

**MS-6-40**

**SERVO MOTOR MS-6-40**



## FEATURES

Dimensions: 40.8 x 20.1 x 38 mm  
Operating Speed: 0.18sec/60degree (4.8V),  
0.16sec/60degree (7V)  
Stall Torque: 5kg.cm/69.56oz.in(4.8V),  
6kg.cm/83.47oz.in(6V)  
Operating Voltage: 4.8V~6V  
Control System: Analog  
Direction: CCW  
Operating Angle: 120degree  
Required Pulse: 900us-2100us  
Bearing Type: 2BB  
Gear Type: Plastic  
Motor Type: Metal  
Connector Wire Length: 30 cm

Servo motor 6kg.cm at 6VDC