



TM3S10-C Cable Tie Mount, Natural, PA 6.6, 0.86x0.61", #10 Screw, PK100

TM3S10-C

Panduit TM3S10-C screw applied cable tie mounts offer a through hole in the mount in which a screw or rivet can be secured, this offers maximum stability for cable bundles. Install with a #10 (M5) screw. Suitable for miniature, intermediate, standard and light heavy cross-section cable ties. Made of Nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. They are 0.61" (15.5mm) wide, are natural in color and come in packages of 100.

Specifications

Material Description	Nylon 6.6
Product Type	Cable Tie Mount
Application	Unique Cradle Design Provides Maximum Stability for the Cable Bundle and Low Profile Design Keeps Bundle Close to Mounting Surface
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Screw-On
Mounting Hole Thread Size	#10
Overall Length (In.)	0.86
Overall Length (mm)	21.9
Overall Width (In.)	0.61
Overall Width (mm)	50.3
Overall Height (In.)	0.37
Overall Height (mm)	9.4
Standards Met	CE Compliant, UL Recognized:E136577, RoHS Compliant
For Use With	Miniature, Intermediate, Standard, Light Heavy Cross-Section Ties

Packaging Detail

UPC	07498358280
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0266
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.1329