



## **TM3S10-C76 Cable Tie Mount, Aqua, ETFE, 0.86x0.61", #10 Screw, PK100**

TM3S10-C76

Panduit TM3S10-C76 Cable Tie Mounts are designed for applications requiring resistance to environmental stresses such as chemical attack, gamma radiation, ultraviolet radiation and extreme temperatures. Ideal for use in nuclear power facilities and chemical processing plants. These mounts can be used with Standard and Light-Heavy cross section cable ties. Use with #10 (M5) screws. For indoor or outdoor use, made of Tefzel, are aqua in color, and come in packages of 100.

### **Specifications**

Material Description	ETFE (Chemical-Resistant, UV-Resistant, Weather-Resistant)
Product Type	Cable Tie Mount
Application	Unique Cradle Design Provides Maximum Stability for the Cable Bundle and Low Profile Design Keeps Bundle Close to Mounting Surface
Color	Aqua
Flammability Rating	UL 94 V-0
Environment	Indoor
Material	ETFE
Maximum Operating Temperature (°C)	170
Maximum Operating Temperature (°F)	338
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Screw-On
Mounting Hole Thread Size	#10
Overall Length (In.)	0.86
Overall Length (mm)	21.7
Overall Width (In.)	0.61
Overall Width (mm)	15.5
Overall Height (In.)	0.37
Overall Height (mm)	9.5
Resistance Properties	Chemical-Resistant, UV-Resistant, Weather-Resistant
Standards Met	CE Compliant, UL Recognized:E136577, RoHS Compliant
For Use With	Standard, Light Heavy Cross-Section Ties

**Packaging Detail**

UPC	07498358275
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0546
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.2728