



Panduit TM3S10-C96A Antimicrobial Met-Det Mount

TM3S10-C96A

Panduit TM3S10-C96A Cable Tie Mounts are designed to help the food and beverage industries meet manufacturing safety standards. In addition to their metal detectability, their antimicrobial properties help to reduce the growth of harmful bacteria fungus and mold on the surface of the part only. These mounts can be used with Standard and Light-Heavy cross section cable ties. Use with #10 (M5) screws. Made of Metal Detectable Nylon 6.6, are blue in color, and come in packages of 100.

Specifications

Material Description	Nylon 6.6 (Antimicrobial)
Product Type	Cable Tie Mount
Application	Unique Cradle Design Provides Maximum Stability for the Cable Bundle and Low Profile Design Keeps Bundle Close to Mounting Surface
Color	Blue
Flammability Rating	UL 94 HB
Environment	Indoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	185
Maximum Operating Temperature (°F)	85
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Mount Method	Screw-On
Mounting Hole Thread Size	#8
Overall Length (In.)	0.87
Overall Length (mm)	22
Overall Width (In.)	0.61
Overall Width (mm)	15.5
Overall Height (In.)	0.37
Overall Height (mm)	9.5
Resistance Properties	Antimicrobial
Standards Met	RoHS Compliant
For Use With	Miniature, Intermediate, Standard, Light-Heavy Cross-Section Ties

Packaging Detail

UPC	61305682378
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0546
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.2728