

Home / Products / Hand Tools / PA2029 DIE 26-14 AWG
INSULATED BLISTER

PA2029 DIE 26-14 AWG INSULATED BLISTER

Cat No: PA2029

UPC No: 769328101010

[Where to Buy](#)

[Contact Sales](#)

For Smaller Wire Barrel Terminals



Specifications

Attribute Name	Attribute Value
Application	For Insulated Terminal Crimpers
Cable Type	Insulated Terminals And Lugs
Connection	Solid Or Stranded Wire, 26 - 14 AWG (0.100 - 2.500 SQ-MM)
Crimp Size	<ul style="list-style-type: none">• 16-14 AWG (1.500 - 2.500 SQ-MM) Blue• 22-18 AWG (0.340 - 0.750 SQ-MM) Red• 22-26 AWG (0.340 - 0.100 SQ-MM) Yellow
Package	Blister
Sub Brand	CrimpALL®
Type	Interchangeable
Item Status Date	01012009
Country of Origin	TW
UNSPSC	43223334
International Harmonize Code	8207306092
RoHS Indicator	U

Attribute Name	Attribute Value
MSDS Update Flag	N

Products

- Cable TV
- Copper-DSL
- Ethernet
- Fiber Optic Instruments
- Hand Tools
- Location and Irrigation
- VDV Instruments
- Adapters

Quick Links

- Request a Demo
- Contact Us
- Join Mailing List
- News
- Where to Buy

Our Company

- About Us
- Jobs
- Paladin



©2020 Tempo Communications, Inc.

[Cookies](#) [License Agreement](#) [Privacy Policy](#)

[Terms & Conditions](#) [Vendor Information](#)