

Home / Products / Hand Tools / PA2040 DIE INSULATED TERM  
AWG 22-12 BLISTER

# PA2040 DIE INSULATED TERM AWG 22-12 BLISTER

**Cat No:** PA2040

**UPC No:** 769328101072

[Where to Buy](#)

[Contact Sales](#)

For Standard Commercial Terminals (Hardware Store Brands)



#### Specifications

Attribute Name	Attribute Value
Application	For Insulated Terminal Crimps
Cable Type	Insulated Terminals And Lugs
Connection	Solid Or Stranded Wire, 22 - 12 AWG (0.340 - 4.000 SQ-MM)
Crimp Size	12-10 AWG (4.000 SQ-MM) Yellow, 16-14 AWG (1.500 - 2.500 SQ-MM) Blue, 22-18 AWG (0.340 - 0.750 SQ-MM) Red
Package	Blister
Sub Brand	CrimpALL®
Type	Interchangeable
Item Status Date	01012009
Country of Origin	TW
UNSPSC	43223334
International Harmonize Code	8207306092

Attribute Name	Attribute Value
RoHS Indicator	U
MSDS Update Flag	N

## Products

- Cable TV
- Copper-DSL
- Ethernet
- Fiber Optic Instruments
- Hand Tools
- Location and Irrigation
- VDV Instruments
- Adapters

## Quick Links

- Request a Demo
- Contact Us
- Join Mailing List
- News
- Where to Buy

## Our Company

- About Us
- Jobs
- Paladin



©2020 Tempo Communications, Inc.

[Cookies](#) [License Agreement](#) [Privacy Policy](#)

[Terms & Conditions](#) [Vendor Information](#)