

Home / Products / Hand Tools / PA2648 DIE MINI-75 BLISTER

# PA2648 DIE MINI-75 BLISTER

**Cat No:** PA2648

**UPC No:** 769328108378

[Contact Sales](#)

Common 2-piece and 3-piece BNC/TNC (Kings, ADC, Amphenol, etc.)



## Specifications

Attribute Name	Attribute Value
Application	For Coaxial Connectors
Cable Type	RG174, RG59/62, Mini-Coaxial 75-ohm
Connection	HDTV SMA, True 75-ohm BNC/TNC, Mini-UHF
Crimp Size	0.255 IN (6.500 MM), 0.197 IN (5.000 MM), 0.178 IN (4.500 MM), 0.068 IN (1.700 MM) HEX and 0.042 IN (1.000 MM) SQ
Package	Blister
Sub Brand	CrimpALL®
Type	Interchangeable
Item Status Date	01012009
Country of Origin	TW
UNSPSC	43223334
International Harmonize Code	8207306092
RoHS Indicator	U
MSDS Update Flag	N

## Products

- Cable TV
- Copper-DSL
- Ethernet

## Our Company

- About Us
- Jobs
- Paladin

- [Fiber Optic Instruments](#)
- [Hand Tools](#)
- [Location and Irrigation](#)
- [VDV Instruments](#)
- [Adapters](#)

### Quick Links

- [Request a Demo](#)
- [Contact Us](#)
- [Join Mailing List](#)
- [News](#)
- [Where to Buy](#)



©2020 Tempo Communications, Inc.

[Cookies](#) [License Agreement](#) [Privacy Policy](#)

[Terms & Conditions](#) [Vendor Information](#)