

[Home](#) / [Products](#) / [Hand Tools](#) / [PA2649 DIE 75-OHMCX BLISTER](#)

PA2649 DIE 75-OHMCX BLISTER

Cat No: PA2649

UPC No: 769328108385

[Contact Sales](#)

Common 2-piece and 3-piece BNC/TNC (Kings, ADC, Amphenol, etc.)



Specifications

Attribute Name	Attribute Value
Application	For coaxial connectors
Cable Type	RG59, RG6, Belden 8281, Belden 1694A
Connection	HDTV BNC/TNC/CATV 'F' True 75-ohm
Crimp Size	0.324 IN (8.200 MM), 0.255 IN (6.500 MM), 0.068 IN (1.700 MM) HEX and 0.052 IN (1.300 MM), 0.042 IN (1.000 MM) SQ
Package	Blister
Sub Brand	CrimpALL®
Type	Interchangeable
Item Status Date	01012009
Country of Origin	TW
UNSPSC	43223334
International Harmonize Code	8207306092
RoHS Indicator	U

Attribute Name	Attribute Value
MSDS Update Flag	N

Products

- Cable TV
- Copper-DSL
- Ethernet
- Fiber Optic Instruments
- Hand Tools
- Location and Irrigation
- VDV Instruments
- Adapters

Quick Links

- Request a Demo
- Contact Us
- Join Mailing List
- News
- Where to Buy

Our Company

- About Us
- Jobs
- Paladin



©2020 Tempo Communications, Inc.

[Cookies](#) [License Agreement](#) [Privacy Policy](#)

[Terms & Conditions](#) [Vendor Information](#)