



Dry Contact Sensor

ACC01

The Dry Contact Sensor integrates with the Panduit G5/G6 iPDU or UPS to offer status change such as motion. The sensor comes with a cable measuring 5.9 feet (1.8 m) and a RJ45 connector. The sensor measures 1.23 inches x 0.70 inches x 0.40 inches (44 mm x 21 mm x 11 mm). The switch is not included.

Specifications

Product Type	Dry Contact Input
Overall Length (In.)	78.74
Overall Length (mm)	2000
Overall Width (In.)	1.2
Overall Width (mm)	30.4
Overall Height (In.)	0.7
Overall Height (mm)	17.7
Environment	Indoor
For Use With	G5, G6, EL2P PDUs and UPS
Standards Met	CE Compliant
Application	Data center rack or cabinet
Color	Black
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Part Features	Contact sensor sends an alarm when contact is changed.

Packaging Detail

UPC	61305631842
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.1667
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000