



Temperature and Humidity Sensor

EB001

The Panduit Temperature and Humidity Sensor seamlessly connects with the Panduit iPDU or UPS to provide temperature and humidity monitoring in a rack. The sensor includes a 6.6 foot (2m) cable and measures 1.23 inches x 0.70 inches x 0.40 inches (44mm x 21mm x 11mm).

Specifications

Overall Length (In.)	81.06
Overall Length (mm)	2059
Overall Width (In.)	1.04
Overall Width (mm)	26.5
Overall Height (In.)	0.51
Overall Height (mm)	13
Product Type	Environmental Sensor
For Use With	G5, G6, EL2P PDUs and UPS
Part Features	Plug and Play digital sensor RJ45 plug Temperature Measuring Range: 0°C - 65°C [32°F - 149°F] Humidity Measuring Range: 10 - 90% RH

Packaging Detail

UPC	61305631829
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.1667
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000