



2-Post Rack, 45RU, #12-24 Threaded E-Rails, Steel, Black

R2PS

The 2-Post rack provides a reliable foundation for mounting telecommunications and data center equipment. The 84 inch tall rack accepts 19-inch wide equipment with mounting rails that have #12-24 EIA universal mounting hole spacing, and printed numbering from the bottom up. A range of cable managers and accessories work with the rack. The 3-inch deep channel rack is UL listed for 1,000 pounds and is made of steel. The rack is 45 RU and black.

Specifications

Note	Rack channel depth is 3" (76mm)
Material	Steel
Mounting Bolt Method	Threaded
Overall Depth (In.)	15
Overall Depth (mm)	381
Overall Width (In.)	20.3
Overall Width (mm)	516
Overall Height (In.)	84
Overall Height (mm)	2134
Channel Depth (In.)	3
Channel Depth (mm)	76.2
Number of Rack Units	45
Mounting Hole Thread Size	#12-24
Rail Number Direction	Bottom Up
Static Load Capacity (kg)	454
Static Load Capacity (lb)	1000
Color	Black
Standards Met	UL 2416, EIA/ECA-310-E, RoHS Compliant
Includes	(12) 3/8-16 x 1" Hex Head Cap Screws, (12) 3/8-16 Hex Nuts, (24) 3/8" Paint Piercing Grounding Washers, (1) Tube of Anti-Oxidizing Paste, (24) 12-24 x 0.5" Slotted Pan Head Steel Screws
Product Type	2-Post Rack
Finish/Coating	Powder-Coated

Packaging Detail

UPC	07498332052
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	1.1991
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000