



## TrueEdge™ Vertical Wall Mount Enclosure, 3RU, Black

WME3BL

The TrueEdge™ Vertical Wall Mount Enclosure provides a comprehensive architecture that allows up to 36" of active equipment depth to be mounted in a low-profile application. The TrueEdge™ has adjustable rails to allow for optimal configuration. This enclosure houses 3RU of passive equipment and 3RU active equipment. 9.5" Depth, 42" Height, Black

### Specifications

Product Type	Wall Mount Enclosure
For Use With	TrueEdge Enclosures
Material	Steel
Mount Method	Wall Mount
Maximum Load Capacity (kg)	90
Maximum Load Capacity (lb)	200
Number of Rack Units	3
Overall Depth (In.)	9.5
Overall Depth (mm)	240
Overall Width (In.)	28.5
Overall Width (mm)	724
Overall Height (In.)	42
Overall Height (mm)	1068
Sub Brand	PanZone®
Color	Black
Standards Met	UL 2416; IP20
Includes	(1) Vertical Wall Mount Enclosure, (1) Pair of Horizontal Active Equipment Rails (3RU), (1) Pair of Angled Passive Equipment Rails (3RU), (4) #12-24 Screws, (4) M5 Thread Forming Screws, (1) Roll of Tak-Ty® Hook and Loop Cable Tie, (2) Keys, (1) Roll of Grommet Edging, (1) Hardware Kit

**Packaging Detail**

UPC	61305677729
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	8.4091
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000