



TMEH-S10-C0 Heavy Duty Cable Tie Mount, Black, UV PA 6.6, Screw, #10, PK100

TMEH-S10-C0

Panduit TMEH-S10-C0 screw applied extra heavy cable tie mounts are designed for use with Panduit extra-heavy cross section cable ties for mounting cable, large wire bundles, or tubular shapes. Their unique cradle design provides maximum stability for cable bundling, routing and the support of large diameter and heavy cable bundles. Install with #10 (M5) screw. For outdoor use, made of Weather Resistant Nylon 6.6. They are 0.72" (18.3mm) wide, are black in color and come in packages of 1000.

Specifications

Material Description	Nylon 6.6 (UV-Resistant, Weather-Resistant)
Product Type	Cable Tie Mount
Application	Unique Cradle Design Provides Maximum Stability for the Cable Bundle and Low Profile Design Keeps Bundle Close to Mounting Surface
Color	Black
Environment	Indoor/Outdoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Screw-On
Mounting Hole Thread Size	#10
Overall Length (In.)	1.62
Overall Length (mm)	41.1
Overall Width (In.)	0.72
Overall Width (mm)	50.3
Overall Height (In.)	0.61
Overall Height (mm)	15.5
Resistance Properties	UV-Resistant, Weather-Resistant
Standards Met	CE Compliant, UL Recognized:E136577, RoHS Compliant
For Use With	Intermediate, Standard, Heavy, Extra Heavy Cross-Section Ties

Packaging Detail

UPC	07498358071
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0668
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.3338