




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION |     |                 |            |            |            |
|----------|-----|-----------------|------------|------------|------------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED   |
|          | A   | INITIAL RELEASE | 08/22/2023 | BZHANG     | GUTTADAURO |





"J1"  
DOUBLE STACKED USB 3.0 TYPE "A"  
FEMALE CONNECTOR  
30u" GOLD PLATED CONTACTS  
NICKEL PLATED SHELL



"J2"  
DOUBLE STACKED USB 3.0 TYPE "A"  
FEMALE CONNECTOR  
30u" GOLD PLATED CONTACTS  
NICKEL PLATED SHELL


"J1" WIRING MAP "J2"



RECOMMENDED  
PANEL CUTOUT

#### NOTES:

- RATING:  
CURRENT: 1.8A (P1,P4,P10, P13 CONTACTS);  
0.25A(REMAINING CONTACTS)  
OPERATING TEMPERATURE: -10 °C TO +70 °C.
- COUPLER SHALL BE TESTED FOR CONTINUITY.
- COUPLER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC PS-0031.

|                                                                                                                                                                                                                   |  |                            |                    |                                                                                                                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------|--------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]                                                                                                                                                      |  | APPROVALS                  | DATE               | <br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
| OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 |  | DRAWN BY<br>B.ZHANG        | 01/21/2022         |                                                                                                                                                                                                |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]      FRACTIONS<br>.XX = ± .02 [.5]      ± 1/32<br>.XXX = ± .005 [.13]      ANGLES ± 1°                                                                         |  | CHECKED BY<br>GUTTADAURO   | 01/21/2022         |                                                                                                                                                                                                |
| THIRD-ANGLE PROJECTION<br>                                                                                                   |  | APPROVED BY<br>GUTTADAURO  | 01/21/2022         |                                                                                                                                                                                                |
| CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY                                                                                                                                                    |  | CATEGORY<br>USB            |                    | PRODUCT DESCRIPTION<br>ECF DOUBLE STACK CPLR, USB 3.0 AF-AF, SHLD                                                                                                                              |
| COLOR VARIATIONS<br>MAY OCCUR                                                                                                                                                                                     |  | SIZE<br>A                  | CAGE CODE<br>43321 |                                                                                                                                                                                                |
| SCALE: NONE                                                                                                                                                                                                       |  | DWG. NO.<br>ECF504-3DSAA-S |                    | REV.<br>A                                                                                                                                                                                      |
| CAD FILE: ECF504-3DSAA-S.SLDDRW                                                                                                                                                                                   |  | SHEET 1 OF 1               |                    |                                                                                                                                                                                                |