


1	2	3	4	5	6	7	8
MOLD TYPE	MOLD NO.	ITEM					
CONN1 OVERMOLD	CPO0241	3,4					

REV.	ECN NO.	DATE	BY	DESCRIPTION
01		Sep/03/2020	Aine Li	RELEASED



AWG	CONN 1		COLOR	CONN 2
24	1	○	WHITE/ORANGE	1
	2	○	ORANGE	2
	3	○	WHITE/GREEN	3
	4	○	GREEN	4
	5	○	WHITE/BROWN	5
	6	○	BROWN	6
	7	○	WHITE/BLUE	7
	8	○	BLUE	8

- NOTES:
- TESTING SPEC.:
COND. RESISTANCE: 3Ω MAX.
INSUL. RESISTANCE: 10MΩ MIN.
TESTING VOLTAGE: 300V DC
 - IP67 WHEN MATED.
 - FOLLOW IPC620 CLASS II STANDARD TO ASSEMBLY AND INSPECTION.
 - RoHS COMPLIANCE.

4.	A/R	TPU, SHORE A 78, NATURAL, HF (A51100057001SD)
3.	A/R	PLASTIC MASTERBATCH,BLACK,FORTPU(A88270010001SD)
2.	2	I/O CONN., MALE, 8P, (A30140235001SD)
1.	A/R	CABLE, CAT.6, UTP PATCH CABLE, #24*4P, OD=5.6
ITEM	QTY	DESCRIPTION

THIS DRAWING CONTAINS CONFIDENTIAL INFORMATION AND IS THE PROPERTY OF SINBON ELECTRONICS CO., LTD. IT MAY NOT BE USED OR ITS CONTENTS COPIED OR DISCLOSED TO A THIRD PARTY WITHOUT PRIOR WRITTEN CONSENT AND IS TO BE RETURNED PROMPTLY UPON REQUEST BY SINBON ELECTRONICS CO., LTD.

CUSTOMER : DigiKey		SINBON SINBON Electronics Co., Ltd.	
CUSTOMER P/N : N/A	REV. N/A	DESCRIPTION : 8P M-M, X code anti-vibe IP67, 3M	
UNLESS OTHERWISE SPECIFIED TOLERANCE :		PART NUMBER : M12X-08CMS00-UL24N30	
1 ~ 10 : ±1	11 ~ 30 : ±2	REV. 01	
31 ~ 50 : ±3	51 ~ 200 : ±5	SIZE UNIT SCALE SHEET	
201 ~ 400 : ±7	> 401 : ±10	A3 mm NONE	1 of 1
ANGLES : ±1°			