

3M[™] Diamond Grade[™] Conspicuity Markings 983-326 (42102606) Red/White, 2 in x 24 in each

3M ID 75030123741, UPC 00051135309582



Specifications

BrandDiamond Grade™ColorRed/White, Red/WhiteLength24 InchTrademarkDiamond GradeWidth2 Inch

Details

- Durable and rigid for easy application, 7 years non-prorated warranty, vivid colors with bright white ensures maximum reflectivity and superior daytime color.
- 3M[™] Diamond Grade[™] Conspicuity Tape is six times brighter than conventional markings. It is the ideal truck tape to use to meet the DOT regulation. 3M's DOT reflective tape is highly durable and non-corroding.
- 3M's DOT tape is certified and guaranteed to meet and exceed NHTSA requirements
- Durable resists weather, dirt and aging
- Available in two product constructions
- Series 983 strong and durable for easy application to smooth surfaces
- Pre-sealed edges
- Non-metallic construction to prevent corrosion

Highly reflective microprismatic sheeting with pressure sensitive adhesive with liner and premask in pre-cut strips for easy application to trucks, trailers and large vehicles. 6 in. red, 6 in white pattern.