

+ CORPORATE HEADQUARTERS Product EOL Notice

August 8, 2018

707 Dayton Road		
PO Box 1040 Ottawa, IL 61350	Model	Description
USA	BB-100M-SBSW1-24	LMR100 RPSMA PLG RT ANGLE TO BLKHD W/ORING 24 IN
p: (800) 346-3119	BB-195M-NMSL-24	LMR195 RPSMA TO N MALE CABLE 2 FEET
f: (815) 433-5109	BB-195M-NMSL-240	LMR195 RPSMA TO N MALE CABLE 20 FEET
	BB-195M-NMSM-24	LMR195 N MALE TO SMA MALE 2 FEET
+ EUROPEAN	BB-195M-NMSM-240	LMR195 N MALE TO SMA MALE 20 FEET
HEADQUARTERS	BB-195M-NMSM-36	LMR195 N MALE TO SMA MALE 3 FEET
	BB-195M-SISM-12	LMR195 SMA F BULKHEAD TO SMA MALE 1 FT
Westlink Commercial Park Unit 10	BB-195M-SISM-120	LMR195 SMA F BULKHEAD TO SMA MALE 10 FT
Oranmore, Co. Galway	BB-195M-SLSW-12	LMR195 RPSMA PLUG TO JACK BULKHEAD 12 IN
Ireland	BB-195M-SLSW-24	LMR195 RPSMA PLUG TO JACK BULK
p: + 353 91 792444	BB-195M-SLSW-6	LMR195 RPSMA PLUG TO JACK BULK 6 IN
f: + 353 91 792445	BB-400M-NMNM-120	LMR400 N MALE TO N MALE 10'
	BB-400M-NMNM-1200	LMR 400 N MALE - N MALE 100FT
+ CELLULAR	BB-400M-NMNM-240	LMR400 N MALE TO N MALE 20 FOOT CABLE
PRODUCTS GROUP	BB-400M-NMNM-480	LMR400 N MALE TO N MALE 40'
Sokolská 71	BB-400M-NMNM-600	LMR400 N MALE TO N MALE 50 FOOT CABLE
562 04 Ústí nad Orlicí III.	BB-400M-NMNM-840	LMR400 N MALE TO N MALE 70 FOOT CABLE
Czech Republic	BB-400M-NMSL-120	LMR400 RPSMA TO N MALE 10' CBL
p: +420 465 521 020	BB-400M-NMSL-24	LMR400 SMA RP PLG TO N MALE 2'
f: +420 464 647 299	BB-400M-NMSL-600	LMR400 RPSMA TO N MALE 50' CBL
	BB-400M-NMTL-24	LMR400 TNC RP PLG TO N MALE 2'

This is the end-of-life announcement for the Radio Frequency cables listed above. We will no longer stock these items. If there is a project requiring this type of cable, we can quote similar cables on a case by case basis.

Product Migration Path:

We are not offering a direct replacement for these cables.

Contact B+B SmartWorx for availability. Full product documentation is available on our website <u>www.advantech-bb.com</u>, or via our support staff: <u>support@advantech-bb.com</u>

Thank You,

Brian Foster | Product Manager