


LUMOTAST FK - Pushbutton with flush lens, rectangular collar housing

1.15.114.966/0000

A notch on the lamp socket identifies the cathode side.


Please include the desired lens in your order.







Other specifications	
Operating life (operations)	1,000,000 cycle
Degree of protection from front side	IP65 (DIN EN 60529)
Operation temperature min.	-25 °C
Ambient temp. operating max. without lamp / LED	+70 °C
Ambient temp. operating max. with lamp /LED	+55 °C
Storage temperature min.	-40 °C
Storage temperature max.	+80 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
Weight	6 g
ROHS compliant	yes
REACH compliant	yes

Panel cut-out




with plug-in socket for PCB









with socket connector

