
FS4500/FS6500 evaluation boards

KTFRDMFS4500-FS6500EVMUG Rev. 4.0 — 12 June 2017

User guide

1 FRDMFS4503CAEVM, FRDMFS6523CAEVM and FRDMFS6522LAEVM evaluation boards





2 Important notice

NXP provides the enclosed product(s) under the following conditions:

This evaluation kit is intended for use of ENGINEERING DEVELOPMENT OR EVALUATION PURPOSES ONLY. It is provided as a sample IC pre-soldered to a printed circuit board to make it easier to access inputs, outputs, and supply terminals. This evaluation board may be used with any development system or other source of I/O signals by simply connecting it to the host MCU or computer board via off-theshelf cables. This evaluation board is not a Reference Design and is not intended to represent a final design recommendation for any particular application. Final device in an application will be heavily dependent on proper printed circuit board layout and heat sinking design as well as attention to supply filtering, transient suppression, and I/O signal quality.

The goods provided may not be complete in terms of required design, marketing, and or manufacturing related protective considerations, including product safety measures typically found in the end product incorporating the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge. In order to minimize risks associated with the customers applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards. For any safety concerns, contact NXP sales and technical support services.

Should this evaluation kit not meet the specifications indicated in the kit, it may be returned within 30 days from the date of delivery and will be replaced by a new kit.

NXP reserves the right to make changes without further notice to any products herein. NXP makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical", must be validated for each customer application by customer's technical experts.

NXP does not convey any license under its patent rights nor the rights of others. NXP products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the NXP product could create a situation where personal injury or death may occur.

Should the Buyer purchase or use NXP products for any such unintended or unauthorized application, the Buyer shall indemnify and hold NXP and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges NXP was negligent regarding the design or manufacture of the part. NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. © 2017 NXP B.V.

3 Getting started

3.1 Jump start

NXP's analog product development boards provide an easy-to-use platform for evaluating NXP products. The boards support a range of analog, mixed-signal and power solutions. They incorporate monolithic ICs and system-in-package devices that use proven high-volume SMARTMOS technology. NXP products offer longer battery life, a smaller form factor, reduced component counts, lower cost and improved performance in powering state of the art systems.

- 1. Go to the relevant Tool Summary Page: http://www.nxp.com/FRDMFS6522LAEVM http://www.nxp.com/FRDMFS6523CAEVM http://www.nxp.com/FRDMFS4503CAEVM
- 2. Review your Tools Summary Page.
- 3. Locate and click:

Jump Start Your Design

4. Download the documents, software and other information.

Once the files are downloaded, review the user guide in the bundle. The user guide includes setup instructions, BOM and schematics. Jump start bundles are available on each tool summary page with the most relevant and current information. The information includes everything needed for design.

3.2 Kit contents/packing list

The FRDMFS6522LAEVM, FRDMFS6523CAEVM and FRDMFS4503CAEVM contents include:

- Assembled and tested FRDMFS65xx board
- Assembled and test FRDM-KL25Z board
- 3.0 ft. USB-STD A to USB-B-mini cable
- · Connector, terminal block plug, 2 pos., str. 3.81 mm
- Connector, terminal block plug, 8 pos., str. 3.81 mm

3.3 Required equipment

The EVM requires the following items:

 Power supply with a range of 8.0 V to 40 V and a current limit set initially to 1.0 A Standard A plug to Mini-B plug USB cable M/M FlexGUI graphical user interface FlexGUI register definition XML file

3.4 EVM overview

The EVM contains two boards:

- FRDMFS4503CAEVB or FRDMFS6523CAEVB or FRDMFS6522LAEVB: These are the evaluation boards available for the FS6500 / FS4500 SBC. The hardware is described in <u>Section 4.5 "Getting to know the hardware"</u>. This document refers to these boards as EVBs.
- FRDM-KL25Z: This board contains the KL25Z MCU. It is plugged into the EVB by means of the Arduino[™] connectors on both boards. The FRDM-KL25Z manages communication between the EVB and a host PC, allowing users to access the EVB's on-board device features and registers. For more information on the FRDM-KL25Z see <u>Section 11 "References"</u>

4 Board description

4.1 Board overview

The FRDMFS4503CAEVB, FRDMFS6523CAEVB and FRDMFS6522LAEVB are hardware evaluation tools supporting system designs based on NXP's FS4500 and FS6500 product families. The EVM allow testing the devices as an integral part of the overall system being developed. They provide access to all FS45xx and FS65xx functions (SPI, IOs) and support functional modes such as debug, normal, buck and boost.

Table 1. EVMs supporting the FS45xx/FS65xx family

EVM name	Supported silicon	Options
FRDMFS6522LAEVM	MC33FS6522LAE	CAN, LIN, No FS1b, V _{CORE} DC/DC 2.2 A ^[1]
FRDMFS6523CAEVM	MC33FS6523CAE	CAN, FS1b, No LIN, V _{CORE} DC/DC 2.2 A ^[1]
FRDMFS4503CAEVM	MC33FS4503CAE	CAN, FS1b, No LIN, V _{CORE} LDO 500 mA

[1] The FRDM board is limited to 1.5 A


4.2 Board features

The main features of the FRDMFS6522LAEVB, FRDMFS6523CAEVB and FRDMFS4503CAEVB evaluation boards are:

- VBAT power supply connector
- VCORE configuration:1.3 V
- VCCA configuration: 3.3 V, using internal PMOS
- VAUX configuration: 5.0 V
- · Buck or boost setting
- DFS configuration
- · Ignition key switch
- CAN bus
- LIN bus (FRDMFS6522LAEVM only)
- FS0B
- FS1B (FRDMFS6523CAEVM or FRDMFS4503CAEVM only)
- IO connector (IO_0 to IO_5)
- Connectivity to KL25Z Freedom board (Access to SPI bus, IOs, LIN digital, RSTB, FS0B, INTB, Debug, MUX_OUT, Regulators)
- LEDs that indicate signal or regulator status

FS4500/FS6500 evaluation boards





4.4 Device features

TheFS65xx/FS45xx are multi-output power-regulating SMARTMOS devices aimed at the automotive market. They include CAN flexible data (FD) and/or LIN transceivers.

Multiple switching and linear voltage regulators—including low-power mode $(32 \ \mu A)$ — provide a variety of wake-up capabilities. An advanced power management scheme maintains high efficiency over a wide range of input voltages (down to 2.7 V) and output current ranges (up to 2.2 A).

The FS45xx/FS65xx family includes enhanced safety features with multiple fail-safe outputs. The devices are capable of fully supporting safety-oriented system partitioning with a high integrity safety level (up to ASIL D).

The built-in CAN FD (flexible data-rate) interface meets all ISO11898-2 and -5 standards. The LIN interface is compliant with LIN protocol specifications 2.0, 2.1, 2.2, and SAEJ2602-2.

Device	Description	Features
FS4500/ FS6500	Automotive control devices	 Battery voltage sensing and MUX output pin Highly flexible SMPS pre-regulator, allowing two topologies: non-inverting buck-boost and standard buck Switching mode power supply (SMPS) dedicated to MCU core supply, from 1.0 V to 5.0 V, delivering up to 2.2 A Switching mode power supply (SMPS) dedicated to MCU core supply, from 1.0 V to 5.0 V, delivering up to 2.2 A Switching mode power supply (SMPS) dedicated to MCU core supply, from 1.0 V to 5.0 V, delivering up to 2.2 A Linear voltage regulator dedicated to auxiliary functions, or to sensor supply (VCCA tracker or independent), 5.0 V or 3.3 V Linear voltage regulator dedicated to MCU A/D reference voltage or I/Os supply (VCCA), 5.0 V or 3.3 V 3.3 V keep alive memory supply available in low-power mode Long duration timer available in low-power mode (1.0 s resolution) Multiple wake-up sources in low-power mode: CAN, LIN, IOs, LDT Five configurable I/Os

Table 2. FS45xx/FS65xxfeatures

4.5 Getting to know the hardware

The primary component of the evaluation boards is the SBC. The boards include an FS45xx or FS65xx and provide full access to all the device's features.

This EVB can either be used alone, or connected to the FRDM-KL25Z board included with this EVM. This provides access to all the features and I/Os of FS45xx/FS65xx through a USB connection.

FS4500/FS6500 evaluation boards




Figure 3. Evaluation board description

Table 3. Board description

Number	Description
1	V _{BAT} connector - Use Phoenix connector to supply board
2	FS45xx / FS65xx
3	Ignition key - Ignition key from car
4	Power supplies - Connector for power supplies (V _{PRE} /V _{CORE} /V _{CCA} /V _{AUX})
5	Power supplies LED - Visualizes regulator state (on or off).
6	V _{DDIO} selection - Selects either V _{CCA} or P3V3_KL25Z (3.3V supply from FRDM-KL25Z board)
7	Enable DBG mode
8	Can & LIN connector - Could be used for debug purpose (CANH, CANL, LIN)
9	I/Os - Input and Output from FS45XX/FS65XX (SPI, V _{PRE} , FS0b, TX LIN)
10	I/Os - Input and Output from FS45XX/FS65XX (IO2, IO3, IO4, IO5, Ignition)
11	I/Os - Input and Output from FS45XX/FS65XX (RSTb, FS1b, DBG, GND, P3V3_KL25Z)
12	I/Os - Input and Output from FS45XX/FS65XX (TX CAN, RX LIN, CAN_5V, V _{CORE} , V _{CCA} , V _{AUX} , V _{KAM} , V _{DDIO})

4.5.1 LED display

The board contains the following LEDs:




Figure 4. LEDs

Schematic label	Name	Color	Description
D8	V _{CORE}	Green	V _{CORE} on
D9	Vkam_IO5	Green	Vkam_IO5 on
D10	V _{PRE}	Green	V _{PRE} on
D11	V _{CCA}	Green	V _{CCA} on
D12	V _{AUX}	Green	V _{AUX} on
D13	RSTb	Red	Enabled when RSTB asserted (logic level = 0)
D14	FS0b	Red	Enabled when FS0b asserted (logic level = 0)
D15	FS1b	Red	Enabled when FS1b asserted (logic level = 0)

4.5.2 Jumper definitions

Figure 5 shows the location of jumpers on the evaluation board.

<u>Table 5</u> describes the function and settings for each jumper. Default jumper settings are shown in bold text.




Table 5. Jumper definitions

Jumper	Description	Setting	Connection/Result
J6	VDDIO selection	[1–2]	VDDIO referenced to V _{CORE} or P3V3_KL25Z
		[2–3]	VDDIO referenced to V _{CCA}
J7	Debug mode	[1–2]	ON:Debug mode OFF: normal mode

4.5.3 Test point definitions

The following test points provide access to various signals to and from the board.

FS4500/FS6500 evaluation boards

FS4500/FS6500 evaluation boards KTFRDMFS4500-FS6500EVMUG




Figure 6. Test points

Table 6. Test point definitions

Test point name	Signal name	Description
TP1	GND	Ground
TP3	RXC	CAN receiver data. Logic level
TP4	INTB	INTB asserted (logic level = 0)
TP5	TXC	CAN transmit data. Logic Level
TP6	RXL	LIN receiver data. Logic level.
TP7	TXL	LIN transmit data. Logic Level

4.5.4 Connectors

Figure 7 shows the location of connectors on the board. The tables below list the pin-outs for each connector.




Figure 7. Connectors

4.5.4.1 V_{BAT} connector (J1)

V_{BAT} connects to the board through Phoenix connector (J1).

Pin number	Connection	Description
1	V _{BAT}	Connects to V _{BAT}
2	Ground	Connects to ground

4.5.4.2 SPI connector (J2_FRDM)

The Debug connector(J2_FRDM) gives access to the FS65xx main signal for debug or experimentation purposes.

Pin number	Connection	Description
1	Not Connected	
2	Not Connected	
3	Not Connected	
4	Not Connected	
5	Not Connected	
6	CSB	SPI chip select, active low

Table 8. SPI connector (J2_FRDM)

Pin number	Connection	Description
7	FS0B	Fail-safe 0.
8	MOSI	SPI Master Output Slave Input
9	Not Connected	
10	MISO	SPI Master Input Slave Output
11	Not Connected	
12	SCLK	SPI serial clock
13	Not Connected	
14	GND	Ground
15	Not Connected	
16	Not Connected	
17	Not Connected	
18	Not Connected	
19	TXL	LIN transmit data. Logic level.
20	Not Connected	

4.5.4.3 CAN and LIN connector (J3)

The CAN and LIN connector is mounted on all three boards, but LIN is supported only on the FRDMFS6522LAEVB.

Table 9. CAN & LINconnector (J3)

Pin number	Connection	Description
1	CANH	Connects to the CANH bus line
2	CANL	Connects to CANL bus line
3	LIN	Connects to the LIN bus
4	GND	Connects to ground

4.5.4.4 Debug connector (J9_FRDM)

The debug connector provides access to DBG as well as FS1b and reset.

Table 10. USB connector (J33)

Pin number	Connection	Description
1	Not Connected	
2	Not Connected	
3	FS1b	Fail-safe 1
4	P3V3_KL25Z	3.3V KL25Z supply
5	Not Connected	
6	Not Connected	
7	Not Connected	
8	P3V3_KL25Z	3.3V KL25Z supply

Pin number	Connection	Description
9	Not Connected	
10	Not Connected	
11	Not Connected	
12	GND	Connects to ground
13	DBG	Debug pin selection
14	GND	Connects to ground
15	RSTB	Reset, active low
16	Not Connected	

4.5.4.5 I/O connector (J1_FRDM)

The I/O connector accesses the device under test (DUT) IO and V_{KAM} signals.

Pin number	Connection	Description
1	Vkam_IO5	Keep alive memory voltage
2	Not Connected	
3	Not Connected	
4	Not Connected	
5	Кеу	Ignition signal
6	Not Connected	
7	IO_2	Input/Output 2
8	Not Connected	
9	IO_3	Input/Output 3
10	Not Connected	
11	IO_4	Input/Output 4
12	Not Connected	
13	Not Connected	
14	Not Connected	
15	Not Connected	
16	Not Connected	

Table 11. I/O connector (J1_FRDM)

4.5.4.6 Power supply connector (J2)

The power supply connector (J2) connects any of the SBC regulators to an external load or board for evaluation purposes.

Table 12. F	ower	supply	connector	(J2)
-------------	------	--------	-----------	------

Pin number	Connection	Description	
1	V _{CCA}	V _{CCA} output voltage	
2	GND	Ground	

© NXP B.V. 2017. All rights reserved.

FS4500/FS6500 evaluation boards KTFRDMFS4500-FS6500EVMUG

Pin number	Connection	Description	
3	V _{AUX}	V _{AUX} auxiliary voltage regulator	
4	GND	Ground	
5	V _{CORE}	V _{CORE} voltage output	
6	GND	Ground	
7	V _{PRE}	V _{PRE} regulator output regulator	
8	GND	Ground	

4.5.4.7 KL25Z ADC inputs (J10_FRDM)

The KL25Z ADCconnector (J10_FRDM) connects the FS6500 regulator outputs to the ADCs on the KL25Z. The regulator values can then be measured and displayed in FlexGUI.

Table 13. KL25Z Analog regulator inputs (J10_FRDM)

Pin number	FRDM Signal	Description
1	Vkam_IO5	Keep alive memory voltage, connected to KL25 ADC0_SE0
2	V _{CORE}	V _{CORE} voltage output, connected to KL25 ADC0_SE8
3	RXL	LIN receiver data. Logic level.
4	V _{AUX}	V _{AUX} auxiliary voltage regulator, connected to KL25 ADC0_SE9
5	VDDIO	Reference voltage for IOs, connected to KL25 ADC0_SE3
6	V _{CCA}	V _{CCA} output voltage, connected to KL25 ADC0_SE12
7	Not connected	
8	CAN_5V	CAN voltage regulator, connected to KL25 ADC0_SE13
9	Not connected	
10	MUX_OUT	Multiplexer output
11	TXC	CAN transmit data. Logic level.
12	Not connected	






Table 14. SW1

Position	Function	Description		
А	GND	Connection between Key input and ground		
В	B Vsup3 Connection between Key input and Vsup3			

5 Board default settings

5.1 V_{CCA} and V_{AUX} setting

 V_{CCA} and V_{AUX} are set by default, respectively to 3.3 V and 5.0 V. It's possible to change that by modifying R26 or R27 (whichever is populated) according to Figure 9.





Figure 9. V_{CCA} and V_{AUX} voltage settings

The V_{AUX} regulator is always tied to the external PNP transistor



5.2 V_{CORE} settings and related configurations

5.2.1 V_{CORE} and F45xx versus FS65xx

The FS45xx family of devices only support V_{CORE} LDO (low dropout) voltage regulators. The FS65xx family only supports V_{CORE} DC/DC voltage regulators. The evaluation board circuitry accommodates this discrepancy by implementing a variation of the BOM for each of the two device families. Populating or not populating resistors with some components depends on which device family is in use and determines which network is enabled.

For the FS45xx family, the following assembly options must be implemented:

- R42: DNP
- C8/C9/R4/D3/L2/C5/C7/R2/C11/R5/C17: populated

For the FS65xx family, it is the opposite:

© NXP B.V. 2017. All rights reserved.

- FS45xx Only R42 DNP Vcore FS65xx Only VSW_Core 2 L2 2.2uH __C6 . 22uF ______ 0.01uF C8 0.1uF C9 180PF R2 200K 0 R3 4.99K GND GND GND D3 R4 PMEG3020EH 15 220 pF FB Core GND R6 8 06K Vcore value (R3) R5 4.99K Vcore = 1.3V 24.9K Vcore = 3.3VComp_core C17 43K Vcore = 5.0VGND 1000pF aaa-025550
- R42: populated
- C8/C9/R4/D3/L2/C5/C7/R2/C11/R5/C17: DNP

Figure 11. V_{CORE} configuration

5.2.2 Compensation network

Both LDO and DC/DC voltage regulators use VCORE voltage feedback to control the output voltage (see Figure 12).


For FS45xx devices using static (steady-state) LDO regulators, a simple resistor bridge (resistors R3 and R6) determines the feedback voltage. By default, the feedback voltage is 1.3 V.

For FS65xx devices using DC/DC voltage regulators, a pair of RC voltage dividers controls the dynamic behavior of the regulator.

5.2.3 FCRBM Resistor Bridge

The feedback core bridge monitoring (FCRBM) Resistor Bridge is an evaluation board safety feature.

The bridge generates the same voltage as the bridge connected to the FB_core pin. If the difference between the two voltages is greater than the VCORE_FB_DRIFT value, the FS state machine is impacted (refer to data sheet). The drift value is set to 1.3V by default.



5.2.4 MCU analog input

To assure the complete isolation of analog signals connected from an external component to the MCU, remove input resistance as applicable for the following:

- V_{PRE} tied to MCU through R83
- V_{CORE} tied to MCU through R98
- V_{AUX} tied to MCU through R90
- V_{CCA} tied to MCU through R94
- CAN_5V tied to MCU through R80
- MUX_OUT tied to MCU through R18
- V_{KAM} tied to MCU through R96

6 Configuring the EVM

6.1 Connecting the hardware

The EVB can be connected to a PC through the FRDM-KL25Z board included with this EVM or any board with an MCU that supports SPI. A power supply with a typical value of 13.5 V must be connected to J1. Regulators can be loaded using J2 connector.

In order to use the board with an FRDM-KL25Z, these steps must be followed for the hardware setup:

Caution: To avoid damaging the board, the V_{BAT} voltage must not exceed 40 V.


- 1. With the power switched off, attach the DC power supply to the Phoenix connector (J1) on the evaluation board.
- 2. A load or an external board can be attached to J2 (not mandatory).
- 3. Plug the board to an FRDM-KL25Z board.



- 4. Connect a USB cable from the USB port labeled **USBKL25Z** on the FRDM-KL25Z board to a USB port on a PC that has the FlexGUI installed.
- 5. Turn on the DC power supply.

Figure 13 illustrates the hardware configuration.

FS4500/FS6500 evaluation boards KTFRDMFS4500-FS6500EVMUG




The software is normally pre-loaded on the KL25Z. For future updates, the procedure for programming the KL25 is described in <u>Section 8 "Appendix A: FRDM-KL25Z software loading"</u>.

7 Software

The FRDMFS4503CAEVB/FRDMFS6523CAEVB/FRDMFS6522LAEVB boards must be plugged into a FRDM-KL25Z. Firmware controlling the communication with the FS45xx/FS65xx must be loaded onto the MCU. The procedure for loading the firmware is described in <u>Section 8 "Appendix A: FRDM-KL25Z software loading"</u>. The FlexGUI graphical user interface that is installed on a PC serves as the user interface to the evaluation board (<u>Section 9 "Appendix B: Installing the FlexGUI</u>"). When connecting the FRDM-KL25Z board to a PC through a USB cable, the following data exchanges are available:

- SPI access (read and write) to FS45xx/FS65xx
- ADC readout, connected to regulators
 - $-V_{PRE}$
 - V_{CORE}
 - V_{AUX}
 - V_{CCA}
 - CAN_5V
 - MUX_OUT
 - V_{DDIO}
 - $-V_{KAM}$
- I/O readout, connected to IO_2 to IO_5
- FS0B/FS1B readout
- RSTB readout
- CAN generated TX signal
- LIN generated TX signal with loopback checking

The software bundle also includes an XML file containing register descriptions for the FS45xx or FS65XX (depending on the evaluation board). This file must be installed in order for the GUI to work properly. In addition, an optional Excel file can be created to facilitate setting several registers at a click.



FS4500/FS6500 evaluation boards

7.1 Creating and using a register configuration file

Creating an Excel register configuration file allows the user to initialize the evaluation board MCU with a predefined set of register values. To create a register configuration file, do the following:

- Open a new Excel spreadsheet file and label the first three columns in row 1 hex, registers and comment. Notice that the first two columns —hex and registers— are mandatory. The comment column is optional.
- 2. In the **hex** column (column A), enter the data or address to be assigned to each register. The address and data must be contained in two bytes and must be expressed as a hexadecimal value. Enter one row per register.
- 3. In the **registers** column (column B), enter the register name associated with the value in the **hex** column.
- 4. In the **comments** column (column C), enter any comments desired. Data in this column is not processed by the FlexGUI. The image below illustrates a typical register configuration file.

	Mandatory		Optional
	+		
	А	В	С
1	Hex	Registers	Comment
2	C424	BIST	ABIST2_VAUX enabled => Start Vaux ABIST
3	CBOC	INIT_FSSM	IO_23_FS Disabled
4			
5			
6		p	
7			
8			
9			
			aaa-025557

5. Launch FlexGUI. When FlexGUI opens, click the **Load Sequence** button to load the register configuration file.

© NXP B.V. 2017. All rights reserved.

Config CPOL CPHA Length StartEt Baud Rate	0 1 16 MSB 7.65 MHz		To Send HEX DEC ASCI BIN	21 33, 100001,	HEX DEC ASCE BIN	21 23, 100001_	140X 0432 A3029 1414	21 33, 10000_	101 102 403	25 33 100001
Received	Purge Bullets		Land Seque			5	end Sert			
	MC21 82W		Pecert				-	IC ANCII	828	
Cear Al	Sevelap	local Log	Case Al	Send in Lange	Load	Send	Our A		e Log	Excel Leg

6. Send the register configuration file to the FS45xx/FS65xx by clicking the **Send Sequence** button.

onverter SPI Converter LUNRT									Contract in the
Cardig CPOL CPINA Langth StartEk Baud Rate	Conveter 0 0 1 16 MSB 7.65 MHz		To Send HEX DEC ASCH BIN	21 33 ₀ 100001 ₀₀	HEX DEC ASCI BIN	21 33, 100001	HDI 010 4201 18	21	33,
	Purge Bullets						ed .		
Pecanved (KEX DEC)	LACIT BIN		Load Seque Recert F545008cm	[ADF2		, Q	Sert Der	ARCEL BER	
Oner Al	Seve Leg	local Log	Over Al	Send In Lamp	Load Sequence	Send Separate	Cear N	Save Log	Excert Long
						\smile			aaa-02564

7.2 Using the FlexGUI

To start the FlexGUI, do the following:

- 1. Configure the hardware as described in Section 6.1 "Connecting the hardware".
- 2. To launch the FlexGUI, execute the .bat file created in <u>Section 9 "Appendix B:</u> Installing the FlexGUI".

7.3 Use case example

This example assumes the user has configured the hardware as shown in Figure 13 and put the evaluation board into debug mode by placing a connector on jumper J15 (see Section 6.1). After launching the FlexGUI, the example configures registers to disable IO_23_FS safety mode, disable the watchdog and release the FSx pins.

 Create an Excel file configured as shown in <u>Table 15</u>. For details on creating an Excel register configuration file, see <u>Section 7.1 "Creating and using a register configuration</u> <u>file"</u>

Table 15		rogistor	configuration	Excel file example
Table 15.	Use case	register	connyuration	Excernie example

HEX	Registers	Comment		
C465	BIST	Execute ABIST2_VAUX and ABIST2_FS1B		
D60C	SF_OUTPUT_REQUEST	Close S1 switch between $V_{\mbox{\scriptsize PRE}}$ and $\mbox{\scriptsize VPU}_{\mbox{\scriptsize FS}}$ to enable FS1B pull up		
CB0C	INIT_FSSM	IO_23_FS Disabled		
8900	INIT_INT	Close main machine initialization sequence		
D34D	WD_refresh_0	1st Watchdog refresh answer		
D29B	WD_refresh_1	2nd Watchdog refresh answer		
D237	WD_refresh_2	3rd Watchdog refresh answer		
D26E	WD_refresh_3	4th Watchdog refresh answer		
D2DC	WD_refresh_4	5th Watchdog refresh answer		
D2B9	WD_refresh_5	6th Watchdog refresh answer		
D372	WD_refresh_6	7th Watchdog refresh answer		
D4A7	RELEASE_FSxB	Release FS0B & FS1B pins		

• To use the register configuration file, open FlexGUI, then load the register configuration file and send it to the evaluation board .

• FlexGUI can now be used to read or write any authorized registers. Below is an example of registers contents:

ead Reg 1 Rea	ad Reg 2 R	lead Reg 3	Read Reg 4	Read Reg 5	Read Reg	6				Write Reg 1 Write	e Reg 2 W	nte Reg 3 N	Vite Reg 4						
INIT_VREG	ICCA_LI	TCCA_	IPFF_DI	VCAN_	RESER	TAUX_L	VALIX_	BATFAI	V	INIT_VREG	ICCA_LI	TCCA_	IPFF_DI	VCAN_	_0	TAUX_L	VAUX_	_0	
INIT_WU1	WU_)00	WU_100	WU_102	WU_102	WU_103	WU_103	WU_104	WU_104		INIT_WU1	WU_100	WU_IO0	WU_102	WU_IO2	WU_IO3	WU_IO3	WU_104	WU_I04	
INIT_WU2	WU_JO5	WU_105	CAN_DI	CAN_W	RESER	LIN_J26	LIN_SR	LIN_SR		INIT_WU2	WU_105	WU_105	CAN_DI	CAN_W	_0	LIN_J26	LIN_SR	LIN_SR	
INIT_INT	INT_DU	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN		INIT_INT	INT_DU	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	
INIT_INH_INT	RESER	RESER	RESER	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	V	INIT_INH_INT	_0	_0	_0	INT_IN	INT_IN	INT_IN	INT_IN	INT_IN	
ONG_DURA	F2	F1	F0	REG_S	LDT_R	MODE	LDT	LDT_IN		LONG_DURA	F2	F1	FO	REG_S	CLEAR	MODE	LDT_E	_0	
HW_CONFIG	LS_DE	RESER	VCCA_	VCCA_	VAUX_	1	DFS_H	DBG_H	V	MODE	VKAM_	LP_OFF	GO_LP	INT_RE	Secure_	Secure_	Secure_	Secure_]
WU SOURCE	10_5_W	10_4_W	10_3_W	10_2_W	10_0_W	AUTO_	LOT_W	PHY_W		REG_MODE	VCORE	VCCA_	VAUX_	VCAN_	Secure_	Secure_	Secure_	Secure_]

aaa-025558

Get regulators and IO values from IOs tab:

FS4500/FS6500 evaluation boards KTFRDMFS4500-FS6500EVMUG

SPI UART	1Os									
Digital IOs IO_0	OUT	•	1	Toggle ID	IO_5	IN		0	Toggle IO	Config Refresh Period DISABLED
10_2	OUT			Toggle ID	DBG	IN			Toggle IO	Analog IOs DISABLED Refresh Period 1 Digital IOs 1
10_3	IN	-	1	Toggle IO	FSOB	IN	•	0	Toggle IO	Single Measurement
10_4	IN	•	0	Toggle IO	FS1B	OUT	•	0	Toggle IO	Purge Buffers
					RSTB	IN	•	1	Toggle IO	
Analog IN					Analog C					Square Generator OUT
VPRE			6.557		AN_OUT	20		-0		Square signal ON/OFF
VAUX			2.379		AN_OUT					
VCCA			5.016			-1		1.0	0	250 kHz
CAN_5V			3.273		AN_OUT					-
MUX_OUT			4.942		AN_001	<u>_</u>		-	0	
X X			4.568		AN_OUT					
x			0.994		na_oor					UT III

aaa-025559

8 Appendix A: FRDM-KL25Z software loading

The quick start package containing the latest firmware can be downloaded from the Downloads tab of the following webpage:


http://www.nxp.com/FRDM-KL25Z

Software loading for the FRDM-KL25Z consists of the following:

- Updating the OpenSDA.
- Programming the FRDM-KL25Z

8.1 Updating OpenSDA

1. Press the RST button and connect the USB (the one marked **SDA**) to the PC.



- 2. LED D4 will start blinking.
- 3. Release the RST button.
- Drag the file FRDM-KL25Z Quick Start Package\OpenSDA Applications/MSD-DEBUG-FRDM-KL25Z_Pemicro_v105.SDA and drop it on the KL25Z board icon which appears as a mass storage device on the host PC.



5. Disconnect the board.

8.2 Programming the FRDM-KL25Z

The software bundle for FRDM_FS6500 includes a **USBtest3.hex** file that programs FRDM-KL25Z with the needed firmware. The procedure is as follows:

- 1. Connect USB (the one marked SDA).
- Drag the file FRDM_FS6500_Test_Package\FRDM_KL25Z_Flash\USBtest3.hex and drop it onto the KL25Z board icon that appears as a mass storage device on the host PC.



3. Unplug the mini USB.

9 Appendix B: Installing the FlexGUI

The FlexGUI graphical user interface provides a PC-based interface for accessing the evaluation board and exercising FS45xx/FS65xx functions. The GUI runs on any Windows 8, Windows 7 or Vista operating system.

To install the FlexGUI software:

- 1. Go to the evaluation board tool summary page
- 2. Under Jump Start Your Design, click on the Get Started with the FRDMFS65xx link.
- 3. From the list of files that appear, click on the **FlexGUI** link. The software downloads to the PC and initiates the installation. An installation wizard guides the user through the process. Upon completion, the GUI executable (FlexGUI.exe), and the relevant register description XML file (in this case, FS65xx.xml) are installed on the system.
- 4. To simplify launching the FlexGUI, create a .bat file with the following commands:

C:\Program Files (x86)\FlexGUI\bin\FlexGUI.exe

C:\Program Files (x86)\FlexGUI\Sequences&Config\FS65xx.xml

10 Schematics, board layout and bill of materials

Board schematics, board layout and bill of materials are available in the download tab of the Tool summary page for the associated board. See <u>Section 11 "References"</u> for links to the relevant Tool summary pages.

11 References

The following URLs reference related NXP products and application solutions:

NXP.com support pages	Description	URL
FS6500-FS4500	Datasheet	https://www.nxp.com/webapp/Download? colCode=FS6500-FS4500
AN5238 - Hardware design and product guidelines	Application note	https://www.nxp.com/webapp/Download? colCode=AN5238
AN4661 - Designing the VCORE Compensation Network	Application note	http://www.nxp.com/files/analog/doc/ app_note/AN4661.pdf
AN4388 - QuadFlat Package (QFP)	Application note	http://www.nxp.com/files/AN4388.pdf
Power dissipation tool (Excel file)	Excel file	http://www.nxp.com/assets/downloads/ data/en/calculators/FS6500-FS4500-power- dissipation-calculator.xlsx
VCORE compensation network simulation board (CNC)		Available on demand
FMEDA	FS6500/FS4500FMEDA	Available on demand
FS6500-FS4500SMUG	FS6500-FS4500SMUG safety manual – User Guide	https://www.nxp.com/webapp/Download? colCode=FS6500-%20FS4500SMUG
FRDMFS6522LAEVM	Tool Summary Page	http://www.nxp.com/FRDMFS6522LAEVM
FRDMFS6523CAEVM	Tool Summary Page	http://www.nxp.com/FRDMFS6523CAEVM
FRDMFS4503CAEVM	Tool Summary Page	http://www.nxp.com/FRDMFS4503CAEVM
FRDM-KL25Z	Tool Summary Page	http://www.nxp.com/FRDM-KL25Z
FS6500	Product Summary Page	http://www.nxp.com/FS6500
FS4500	Product Summary Page	http://www.nxp.com/FS4500
Analog home page	NXP website	http://www.nxp.com/analog

12 Contact information

Visit <u>http://www.nxp.com/support</u> for a list of phone numbers within your region. Visit <u>http://www.nxp.com/warranty</u> to submit a request for tool warranty.

13 Revision history

Revision	Date	Description of changes
1.0	11/2016	Initial release
2.0	11/2016	 Removed content, supporting data and external references for FRDMFS6522LAEVM and FRDMFS6522LAEVB in Section 3.1, Section 3.2, Section 3.4, Section 4.1, Table 1, Section 4.2, Section 4.5.4.3, Section 7 and Section 11 Updated Section 5.1 to reference Figure 9 Updated Section 7.1, item 4 to reference the image Updated Section 7.3 referring user to Figure 13, Section 6.1 and Table 15 Updated external link found in Section 8 Updated URL destinations in Section 11
3.0	6/2017	Updated content to include FRDMFS6522LAEVM
4.0	6/2017	Minor correction (replaced FRDM-KL43Z by FRDM-KL25Z) in <u>Section 8</u>

14 Legal information

14.1 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

14.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXF Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any

liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Suitability for use in automotive applications — This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Evaluation products — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer. In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages. Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

14.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP — is a trademark of NXP B.V.

FS4500/FS6500 evaluation boards

Tables

Tab. 1.	EVMs supporting the FS45xx/FS65xx family	5
Tab. 2.	FS45xx/FS65xxfeatures	. 7
Tab. 3.	Board description	. 8
Tab. 4.	LEDs	9
Tab. 5.	Jumper definitions	10
Tab. 6.	Test point definitions	11
Tab. 7.	VBAT Phoenix connector (J1)	12
Tab. 8.	SPI connector (J2_FRDM)	

	CAN & LINconnector (J3) USB connector (J33)	
	I/O connector (J1_FRDM)	
	Power supply connector (J2)	
	KL25Z Analog regulator inputs (J10_FRDM)	
	SW1	. 10
Tab. 15.	Use case register configuration Excel file	~-
	example	.25

Figures

Fig. 1.	FRDMFS6523CAEVM	1
Fig. 2.	FRDMFS65/FRDMFS45 block diagram	6
Fig. 3.	Evaluation board description	8
Fig. 4.	LEDs	9
Fig. 5.	Jumpers	10
Fig. 6.	Test points	11
Fig. 7.	Connectors	12

Fig. 8.	Switches	16
Fig. 9.	VCCA and VAUX voltage settings	17
Fig. 10.	VAUX regulator	17
Fig. 11.	VCORE configuration	18
Fig. 12.	FCRBM Resistor Bridge	19
Fig. 13.	Evaluation board hardware configuration	
Fig. 14.	Software overview	22

Contents

1	FRDMFS4503CAEVM, FRDMFS6523CAEVM and FRDMFS6522LAEVM evaluation boards	1
2	Important notice	
3	Getting started	3
3.1	Jump start	
3.2	Kit contents/packing list	
3.3	Required equipment	
3.4 3.4	EVM overview	3 ار
3. 4 4	Board description	
4 4.1	Board overview	
4.1 4.2	Board features	
4.2 4.3		
	Block diagram	
4.4	Device features	
4.5	Getting to know the hardware	
4.5.1	LED display	
4.5.2	Jumper definitions	
4.5.3	Test point definitions	
4.5.4	Connectors	
4.5.4.1	VBAT connector (J1)	
4.5.4.2	SPI connector (J2_FRDM)	
4.5.4.3	CAN and LIN connector (J3)	
4.5.4.4	Debug connector (J9_FRDM)	
4.5.4.5	I/O connector (J1_FRDM)	
4.5.4.6	Power supply connector (J2)	. 14
4.5.4.7	KL25Z ADC inputs (J10_FRDM)	. 15
4.5.5	Switches	
5	Board default settings	
5.1	VCCA and VAUX setting	
5.2	VCORE settings and related configurations	
5.2.1	VCORE and F45xx versus FS65xx	
5.2.2	Compensation network	
5.2.3	FCRBM Resistor Bridge	
5.2.4	MCU analog input	
6	Configuring the EVM	
6 .1	Connecting the hardware	
7	Software	
7 .1	Creating and using a register configuration	. 22
1.1	file	23
7.2	Using the FlexGUI	
7.2 7.3	Use case example	
8	Appendix A: FRDM-KL25Z software loading	
8.1	Updating OpenSDA	
8.2	Programming the FRDM-KL25Z	
9	Appendix B: Installing the FlexGUI	. 28
10	Schematics, board layout and bill of	
	materials	
11	References	
12	Contact information	
13	Revision history	
14	Legal information	. 32

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2017.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 12 June 2017