P1: M-042
P2: M-043

Customer No.:	No.:1



P1,P2: E210037-VN

* NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

PACKING A: ≤1FT

PACKING B: ≤2FT

PACKING C: >2FT



MARKING: (UL) SJT 3/C 12AWG(3.31MM^2) VW-1 105°C 300V E204978

C(UL) SJT 3/C 3.31MM^2(12AWG) FT2 105°C 300V E204978 MSL-VN-

119120B2F12A(FP212-00)

	P1		P2
BLACK	L	———	L
WHITE	N	———	N
GREEN	E	———	E

No.	DESCRIPTION		Q'TY	Supplier
3	UL SJT 12AWG x 3C, OD 11.0mm, JACKET BLACK, DRAWING No.EPSJT011203C-158	H5TC41-0304K09	L-20mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304		M304
	BRACKET: YST-038	A1QC79-0767K09	1Set	M767
	TERMINAL: 97607BS-1	A1QB35-0257	1	M257
	TERMINAL: 97606BS-1	A1QB34-0257	2	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304	1	M304
	BRACKET: YST-037	A1QC36-0767K09	1Set	M767
	TERMINAL: 98739ABS-0	A1QB33-0257	3	M257

9 REV.9 2024.07.17	MODIFY ITEM NO AND PACKING		
7 REV.7 2023.05.31	MODIFY P2 MOLDED LOGO	8 REV.8 2023.06.06	MODIFY P2 MOLDED LOGO
5 REV.5 2017.07.20	MODIFY CABLE	6 REV.6 2021.11.15	MODIFY MARKING
3 REV.3 2015.01.29	MODIFY MOLDED	4 REV.4 2015.10.12	MODIFY MOLDED
1 REV.1 2012.10.19	MODIFY MOLDED	2 REV.2 2012.10.30	MODIFY PACKING

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

APPROVED		CompuCableUSA	
CHECKED	HU		
DESINGER	XJW		
DRAWING	MuMu		
DATE	17/JUL/24	ITEM NO.	9 AC-12-192XX

Cable Length
Unless Other Spec.
Tolerances:

0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm

UNIT:mm