P1: M-003
P2: M-005

Customer No.:	No: 1



NEMA 5-15P (MSL-105)

IEC 320 C13(MSL-107)

PACKING A: <3M



PACKING B: >3M





P1,P2: c UL us E210037-VN

*NOTE: All relevant materials are complied with RoHS directive .

THE CABLE MARKING IS CONCAVE LETTERING MOULD

MARKING:

(UL) SVT 3/C 18AWG(0.824MM^2) SHIELDED 105°C 300V E204978

C(UL) SVT 3/C 0.824MM^2(18AWG) SHIELDED 60°C 300V E204978

MSL-VN-

市場部 2023.08.04 屈飛霞

105107B1S18A(FP020-00)

	P1		P2
BLACK	L	———	L
WHITE	N	———	N
GREEN+DRAIN	E	———	E

No.	DESCRIPTION		Q'TY	Supplier
3	UL SVT 18AWG x 3C+S, OD 6.3mm, JACKET BLACK, DRAWING No. EPSVTAL1803C-006	H5TB03-0304K09	L-30mm	M304
2	MOLDED PVC BLACK, 35P	H1BC02-0304K09		M304
	BRACKET: YS-003	A1QC14-0767	1	M767
	TERMINAL: 2*4mm, 98744BS-0/A	A1QB55-0257	3	M257
1	MOLDED PVC BLACK, 35P	H1BC02-0304K09		M304
	BRACKET: YS-002, WHITE	A1QC07-0767W09	1	M767
	TERMINAL: 98661BS-1	A1QB01-0257	2	M257
	TERMINAL: ø4.75mm, 98475BS-1	A1QB06-0257	1	M257

5 REV.5 2022.01.18	MODIFY MARKING AND ELEMENT NO	6 REV.6 2023.08.03	MODIFY MARKING
3 REV.3 2017.06.12	MODIFY MSL-107 MOLDED SIZE	4 REV.4 2017.09.28	MODIFY PLUG LOGO & CABLE MARKING
1 REV.1 2013.02.01	MODIFY PLUG POINT AT	2 REV.2 2015/3/3	MODIFY PLUG LOGO

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

APPROVED	
CHECKED	HU
DESINGER	ZHU
DRAWING	PLS
DATE	3/AUG/23

CompuCableUSA

AC-012XX-SH

Cable Length Unless Other Spec. Tolerances:

0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm

UNIT:mm