




Item (Detail view)

End and intermediate plate; 1 mm thick

Item no.	2004-1432	GTN / EAN	4044918390880
Content	1 piece	Order unit	piece
Order quantity	25 piece	Increase in order quantity	(25, 50, 75, 100, ...)
Customer item no.		Customs tariff no.	8538909990
Customs duty for the country of origin	CN	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS Compliant



Article details Approvals Downloads/Certificates

Description		End and intermediate plate; 1 mm thick																																					
Remarks																																							
Item properties		Miscellaneous																																					
	<table border="1"> <thead> <tr> <th>Name</th> <th>Value</th> <th>Unit</th> </tr> </thead> <tbody> <tr> <td>Width</td> <td>1 mm / 0.039 in</td> <td></td> </tr> <tr> <td>Height</td> <td>32.9 mm / 1.295 in</td> <td></td> </tr> <tr> <td>Depth</td> <td>79 mm / 3.11 in</td> <td></td> </tr> <tr> <td>Color</td> <td>orange</td> <td></td> </tr> <tr> <td>Fire load (MJ)</td> <td>0.072</td> <td>MJ</td> </tr> <tr> <td>Weight (g)</td> <td>2.395</td> <td>g</td> </tr> <tr> <td>Packaging</td> <td>BOX</td> <td></td> </tr> <tr> <td>Type</td> <td>1</td> <td>mm</td> </tr> <tr> <td>Product Family</td> <td>TOPJOB8</td> <td>S</td> </tr> <tr> <td>Main product function</td> <td>End plate</td> <td></td> </tr> <tr> <td>Product type</td> <td>Accessories</td> <td></td> </tr> </tbody> </table>	Name	Value	Unit	Width	1 mm / 0.039 in		Height	32.9 mm / 1.295 in		Depth	79 mm / 3.11 in		Color	orange		Fire load (MJ)	0.072	MJ	Weight (g)	2.395	g	Packaging	BOX		Type	1	mm	Product Family	TOPJOB8	S	Main product function	End plate		Product type	Accessories			
Name	Value	Unit																																					
Width	1 mm / 0.039 in																																						
Height	32.9 mm / 1.295 in																																						
Depth	79 mm / 3.11 in																																						
Color	orange																																						
Fire load (MJ)	0.072	MJ																																					
Weight (g)	2.395	g																																					
Packaging	BOX																																						
Type	1	mm																																					
Product Family	TOPJOB8	S																																					
Main product function	End plate																																						
Product type	Accessories																																						

Upwards