




2-conductor through terminal block, suitable for Ex e II applications

Item no.	2002-1203	GTN / EAN	4044916081375
Content	1 piece	Order unit	piece
Order quantity	100 piece	Increase in order quantity	(100, 200, 300, 400, ...)
Customer item no.		Customs tariff no.	85369010000
Customs duty for the country of origin	DE	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS Compliant



Article details Approvals Downloads/Certificates Accessories

Description 2-conductor through terminal block, suitable for Ex e II applications

Remarks

Item properties

Miscellaneous

Name	Value	Unit
Packaging type	BOX	
Standards	IEC/EN 60947-7-1	
Rated voltage (III / 3) [V]	800	V
Rated impulse voltage (III / 3) [kV]	8	kV
Rated current [A]	24	A
Rated current (2) [A]	32	A
Rated voltage EN (Ex e II) [V]	550	V
Rated current (Ex e II) [A]	22	A
Rated current (Ex e II) with jumper [A]	20	A
Legend (ratings)	(III / 3) a. Overvoltage category III Pollution degree 3	
Type of wiring	Front-entry wiring	
Total number of connection points	2	
Total number of potentials	1	
Number of levels	1	
Connection technology	Push-in CAGE CLAMP®	
Actuation type	Push-in	
Connectable conductor materials	Copper	
Nominal cross section	2.5 mm²	
Solid conductor	0.25 ... 4 mm² / 22 ... 12 AWG	
Solid conductor, push-in termination	0.75 ... 4 mm² / 18 ... 12 AWG	
Fine-stranded conductor	0.25 ... 4 mm² / 22 ... 12 AWG	
Fine-stranded conductor with ferrule, push-in termination, f	0.75 mm² / 18 AWG	
Strip length	10 ... 12 mm / 0.39 ... 0.47 inch	
Width	5.2 mm / 0.205 inch	
Height from upper edge of DIN-35 rail	32.9 mm / 1.295 inch	
Depth	48.5 mm / 1.909 inch	
Design	horizontal	
Type of mounting	Carrier rail 35 x 15	
Marking level	Center-side marking	
Color	red	
Insulating material	Polyamide 66 (PA 66)	
Fire load [MJ]	0.109	MJ
Weight [g]	5.079	g
Product Family	TOPJOB® S	
Main product function	Through term. block	
Product type	Through rail mount term. blocks	