

MultiTask Surface Cleaner MultiClean™



- 70% High Purity Grade Isopropyl Alcohol (IPA) and 30% High Purity Deionized (D.I.) Water
- Purified D.I. water reduces evaporation rate for more effective cleaning
- Suitable for cleaning a variety of surfaces and the general working environment
- Removes solder paste, white residue, flux residues, uncured epoxy residues, light oils and grease
- · Mild and not harmful to skin
- · Wide spray pattern to maximize coverage
- · Leaves no residue; ESD-safe

Product Information

MultiTask Surface Cleaner – *MultiClean*, provides fast and safe cleaning in almost any production environment. High purity IPA and D.I. water is well suited for cleaning medical devices, electronics, stencils, work benches, tools, production machinery, and any surface that requires hygienic grade cleaning.

This versatile cleaner effectively removes white residue from PCBs, as well as most solder pastes found on SMT stencils. It also cleans organic and ionic residues, light oils and other contaminants commonly found in the manufacture of medical devices. With excellent materials compatibility, it is both safe and easy to use.

Technical Details & Cleaning Data				
Boiling Point	82°C / 180°F			
Chemical Family	Water & Alcohol			
Cleaning Strength (KB value)	25 (est.)			
Evaporation Rate	Slow			
Odour	Slight, Alcohol			
Percent Volatile	100%			
Specific Gravity	.87 g/mL			
Health, Safety & Environmental Data				
Flammable	Yes			
Flashpoint	12°C / 54°F			
NFPA	Health: 1 Fire:3 Instability: 1			
Volatile Organic Content	719 g/L			
RoHS & WEEE	Compliant			
REACH	Compliant			
US EPA SNAP	Approved			
GHS / HCS Pictogram				
Packaging				
Aerosol - 400mL / 308g	MCC-MLC117			
Aerosol Packaging	12 cans / box			
Recycle	40) FE			

Directions:

Hold can approximately 10-15cm away from substrate. Spray liberally over area or part to be cleaned. Wipe using a durable clean lint-free wipe.

Lint-Free Wipes

Description	Part Number	Size	Packaging
General Purpose	MCC-W66	152mm x 152mm	50 Sheets/Bag
Wipes	MCC-W99	228mm x 228mm	300 Sheets/Bag
	MCC-W11	216mm x 279mm	100 Sheets/Bag

AVAILABILITY:

Only available in EMEA. Contact MicroCare for a distributor near you. For more information contact MicroCare directly or visit www.MicroCare.com.

Not all products and packages available in all regions and territories.