



G31 Portable External SSD

“Rugged, Durable, Adaptable for Any Situation”-appleinsider

Fantom Drives G31 Portable External SSD Series is blazing fast with transfer speeds up to 560MB/s. Using USB 3.2 Generation 2 Type-C connectivity, you can expect high performance with any creative suite. Lightning fast data transfer rates support applications in photography, 4K video storage and editing, music and large file storage. G31 Portable SSD Series comes with both USB Type A to Type C and Type C to Type C cables. It is compatible with USB 3.2 Generation 2 and Thunderbolt 3 ports while being fully backward compatible with USB 2.0, USB 3.0. Works great for both Mac and Windows.



4.6"

3.2"



0.6"



USB 3.2
Generation 2



Up to 560MB/s
Transfer Speeds



High Quality
Aluminum

Budget Friendly Without Compromise

G31 SSD is made for everyday use with Desktops, Laptops, Xbox One, PlayStation 4 and many different devices. Made budget friendly, G31 does not sacrifice quality and reliability and uses the best chipset and SSD in the market. G31 offers best in class 5 year warranty across all capacities.

Product Engineering

Sleek, Strong Aluminum


The hard bodied aluminum provides maximum protection and durability. It was designed to be sleek and compact in size to allow for grand adventures or everyday use. The 1/16" aluminum casing also doubles as a heat sink allowing the G31 to operate fan-free and silently. With shock resistant and high quality aluminum, the solid state drive can remain intact and not shaken or easily broken like most common drives.

Reliable Storage for PC or Mac

Compatible with Windows (Vista, 7, 8, 10 or newer), Mac OS X or newer (great for MacBook Pro /Time Machine backup), PlayStation (PS4), Xbox One (Original, S, X). The G31 comes in varying capacities, 250GB, 500GB, 1TB, 2TB and 4TB.


USB Type-C and A Compatible

G31 keeps both legacy and new devices in mind. It comes with both USB Type-C to C and USB Type-C to A to allow use with both present and new technology.



File Transfer Speed

Read speed from G31 to Mac or PC: 560MB/s
Write speed from Mac or PC to G31: 500MB/s





Compatibility and Warranty

- Fantom Drives G31 Portable External SSD comes preformatted for Mac or Windows. Simply select the model made specifically for your system. Plug and Play for no hassle, out of the box usage.
- Windows Vista, 7, 8, 10 and Later, Mac OS X 10.6 and Later, PS4, Xbox.
- 5 year limited warranty.

Product Specifications

Interface	USB 3.2 Generation 2 Type-C			
Format	Plug and Play with Windows - NTFS Plug and Play with Mac - HFS+			
Compatibility	Windows Vista, 7, 8, 10 and Later, Mac OS X 10.6 and Later, PS4, Xbox			
Hardware Information	Capacities	250GB, 500GB, 1TB, 2TB, 4TB		
	Dimensions	4.6" x 3.2" x 0.6"		
	Weight	6 oz		
Performance	Up to 560MB/s Read and 530MB/s Write			
Certifications	CE, FCC, RoHS			
Warranty	5 Years Limited Warranty			
SKUs	Mac		Windows	
	Silver	Black	Silver	Black
	CSD250S-M	CSD250B-M	CSD250S-W	CSD250B-W
	CSD500S-M	CSD500B-M	CSD500S-W	CSD500B-W
	CSD1000S-M	CSD1000B-M	CSD1000S-W	CSD1000B-W
	CSD2000S-M	CSD2000B-M	CSD2000S-W	CSD2000B-W
	CSD4000S-M	CSD4000B-M	CSD4000S-W	CSD4000B-W