

## Marker for terminal blocks - UM3-TM (8X8) - 0830929

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Markers for marking terminal blocks from Wieland, 14-section, unmarked, can be marked with THERMOMARK CARD and BLUEMARK, color: white



The figure shows version

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	1.9 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Length (b)	8 mm
Width (a)	8 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

#### General

Color	white
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V2
Material	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	14
Number of individual labels per row	7
Number of marker strips	2
RoHS compliant	Yes
Printability	Thermal transfer
	UV LED technologie

# Marker for terminal blocks - UM3-TM (8X8) - 0830929

## Technical data

### General

Device	5146464 THERMOMARK CARD
	5147999 BLUEMARK CLED
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Marking mounting type	clip on

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

### Classifications

#### eCl@ss

eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

#### ETIM

ETIM 5.0	EC000761
----------	----------

### Accessories

Accessories

Magazine

## Marker for terminal blocks - UM3-TM (8X8) - 0830929

### Accessories

Magazine - TMP-UM-MAG6 - 0803329



Magazine for the THERMOMARK CARD printer, for accommodating UM material (UM3-TM)

---

Magazine - BLUEMARK MAG UM-TM - 0803335



Magazine for the BLUEMARK printer, for accommodating UM materials

---

---