

ABS Plastic - Soft Sided Hand Held Enclosures (1553 Series) - NEW Colors

Products

Technical

Translucent Blue

Contact Us Other Options

Path: Home > Enclosure Index > ABS Plastic - Soft Sided Hand Held - NEW Colors









click to enlarge

click to enlarge

click to enlarge

click to enlarge


Key Features:


- · Ergonomically designed for hand-held comfort.
- Choice of two versions (with or without battery door & compartment) in two sizes.
- Choice of FOUR NEW colors:
 - o black
 - o translucent blue (translucent to blue, white and near white LEDs, readouts & displays)
 - o red
 - o "safety" yellow
- For more color options see our original 1553 series.
- Molded in general purpose ABS plastic with a black overmold, soft plastic grip.
- Top cover is recessed for membrane display or keypad.
- P.C. board standoffs are molded into case (see drawings or photos for more details).
- Includes removable front panel (for easy modifications) and assembly hardware.
- Battery door & compartment version includes 4 battery clips (for 2 AA batteries) and a 9 volt (PP3) battery clip.
- Link here to photo tables of each part number (enclosures shown in Translucent Blue).

Part Number	Enclosure Color	Soft Side Color		2.16.5		.zip File Size		File Size	Battery Door & Compart ment	Units	Overall Dimensions			Max. P.C. Board	
											Length	Width	Enclosure Depth (assembled)	Length	Width
1553BTBUBK 1553BRDBK	Black TransBlue Red	Black	FOF	350K	ZIP	362K	3D ZIP	1.9M	No	Inches		3.11	0.95	4.3	2.4
1553BYLBK	Yellow									mm	117	79	24	109	61
1553DTBUBK	Black TransBlue Red Yellow	Black	205	571K	ZIP	397K	3D ZIP	2.8M	No	Inches	5.8	3.5	0.98	5.48	2.65
1553DYLBK										mm	147	89	24	139	67
1553BTBUBKBAT	Black TransBlue Red	Black	FOF	600K	ZIP	420K	3D ZIP	2.0M	Yes	Inches	4.62	3.11	0.95	3.08	2.4
1553BYLBKBAT	Yellow									mm	117	79	24	78	61
1553DTBUBKBAT	Black TransBlue Red Yellow	Black	207	649K	ZIP	435K	3D ZIP	2.4M	Yes	Inches	5.8	3.5	0.98	4.2	2.65
1553DYLBKBAT										mm	147	89	24	107	67

Link here to photo tables of each part number (enclosures shown in Translucent Blue)

Features (by photo):







catalog pages on this series (626K) 1553Broch.pdf

Accessories

ProtoBoard Printed Circuit Boards:



click to enlarge

- High quality FR4 glass epoxy board
- Specifically designed to fit enclosures shown in the table below
- Mounting screws included
- Lead free etched copper PCB with a flux coating for easy soldering
- 0.042" holes drilled on 0.1" centers
- For more information link to the BPS (BusBoard Prototype Systems) website www.busboard.net

Part Number	Use With Enclosures (above)	BPS Part Number	
1553BPCB	1553B series	PR1553B	
1553DBPCB	1553DBAT series	PR1553DB	

Belt / Pocket Clip Option:





- Molded from tough nylon (choice of Black or Grey).
- Includes 2 nylon screws (insulated to avoid internal interference).
- Mounting template included.

Black - Part Number **1599CLIP**Grey - Part Number **1599CLIPGY**

IR Panel Option:

- Replaces existing front plastic panel.
- Dark red plastic filter (transparent to IR).

For all 1553 "B" sized enclosures - Part Number 1553BIR-BULK For all 1553 "D" sized enclosures - Part Number 1553DIR-BULK

Exactly what you are looking for??? Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

Order from your favorite distributor

Home | Products | Distributors | Technical | Contact Us | Other Options

Copyright; © 2007-2009 Hammond Mfg Co Inc URL: http://www.hammondmfg.com