

IE-FC-IP-1ST/1D9/1D25**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Insert plate, unshielded, 1x Data, 2x Signal
Order No.	1450650000
Type	IE-FC-IP-1ST/1D9/1D25
GTIN (EAN)	4050118255348
Qty.	1 pc(s).

IE-FC-IP-1ST/1D9/1D25

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Technical data

www.weidmueller.com

Dimensions and weights

Height	23 mm	Height (inches)	0.906 inch
Width	51.5 mm	Width (inches)	2.028 inch
Length	90.5 mm	Length (inches)	3.563 inch
Net weight	15 g		

Temperatures

Operating temperature -40 °C...70 °C

Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3	SCIP	67cf1078-beca-4687-860b-dc475a6ec24a
------------	--	------	--------------------------------------

General data

Material	Polycarbonate PC	Product type	Insert plate, unshielded
----------	------------------	--------------	--------------------------

Inserts

Insert, data	1	Insert, signal, D-Sub, 25-pole	1
Signal insert D-Sub 9-pole / VGA / HDMI	1		

General standards

Certificate No. (CSA)	2000039-80039714	Certificate No. (DNVGL)	TAA000022B
Certificate No. (cURus)	E223801		

Classifications

ETIM 6.0	EC000456	ETIM 7.0	EC000456
ETIM 8.0	EC000456	ECLASS 9.0	27-18-28-06
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-28-06
ECLASS 11.0	27-18-28-06	ECLASS 12.0	27-18-28-92

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

IE-FC-IP-1ST/1D9/1D25

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[GL_FrontCom](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

IE-FC-IP-1ST/1D9/1D25

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings

Dimensioned drawing

