

Data sheet | Item number: 850-814/002-000


IP65 enclosure; Sheet steel (RAL 7035); WxHxD (200x120x200 mm); without flange plate



www.wago.com/850-814/002-000



 Picture differs from the item.



Item description

* Notice:

Fieldbus coupler and end modules must be taken into account!

This applies to 12 mm wide I/O modules. I/O modules with a width of 24 mm count as two I/O modules.

Included:

- Powder-coated, sheet steel enclosure
- Box with narrow beveled edge, sturdy gutter profile
- With hinged cover 180° (PA), with foam PU seal, 2 to 3 quick disconnects
- Quick-release fasteners in plastic bushes
- Mounting holes (incl. sealing plugs)
- Large Macrolon inspection glass
- Removable, yellow-chromized interior profiles

—
Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



- Galvanized DIN-35/7.5 rail (contact with enclosure), adjustable in 12.5 mm spacing
- Grounding lug for cover and flanges with quick-release ribbon cable connectors
- Light gray (RAL 7035)

Accessories:

Fitted and unfitted flange plates, wall mounting

Data

Technical data

Number of I/O modules	8
Accessories for flange plates (available separately)	1 x F200 or F200-1 or F200-2 or F204

Physical data

Width	200 mm / 7.874 inch
Height	120 mm / 4.724 inch
Depth	200 mm / 7.874 inch
Panel cutout (W x H)	(160 x 160) mm

Material data

Weight	2125 g
--------	--------

Environmental requirements

Protection type	IP65
-----------------	------

Commercial data

PU (SPU)	1 Stück
Packaging type	box
Country of origin	DE
GTIN	4055143243087
Customs tariff number	85381000900

Downloads

Documentation

Bid Text

850-814/002-000	Oct 9, 2017	doc	Download
-----------------	-------------	-----	----------

Subject to changes. Please also observe the further product documentation!



doc - Datei			32.3 kB	
850-814/002-000		Feb 19, 2019	xml	Download
X81 - Datei			4.4 kB	

System Description

IP65 System Housing			pdf 490.1 kB	Download
---------------------	--	--	-----------------	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 850-814/002-000			URL	Download
IP65 enclosure; Sheet steel (RAL 7035); WxHxD (200x120x200 mm); without flange plate				

Installation Notes

Subject to changes. Please also observe the further product documentation!