

**FUSE 1KV DC 10A 10/38****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 10x38 mm in sizes from 2 A to 20 A.

**General ordering data**

Version	Accessories, Fuse
Order No.	<a href="#">1224910000</a>
Type	FUSE 1KV DC 10A 10/38
GTIN (EAN)	4050118008746
Qty.	10 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2022-03-31
Alternative product	<a href="#">2783230000</a>

## FUSE 1KV DC 10A 10/38

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmuller.com](mailto:info@weidmuller.com)

[www.weidmuller.com](http://www.weidmuller.com)

## Technical data

### Dimensions and weights

Depth	10 mm	Depth (inches)	0.394 inch
Height	38 mm	Height (inches)	1.496 inch
Width	10 mm	Width (inches)	0.394 inch
Diameter	10 mm	Net weight	9 g

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	e55693ba-5f1b-4f6e-b99e-8d57d3de2235
------------	----------------	------	--------------------------------------

### Material data

Colour	white
--------	-------

### System specifications

Version	Fuse cartridge
---------	----------------

### Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

### Dimensions

Diameter	10 mm
----------	-------

### Fuse cartridges

Cartridge fuse	10 x 38 mm	Characteristics	slo-blo
Colour	white	Current	10 A
Melting integral	7 A <sup>2s</sup>	Power output (@ 1.5 In)	2 W
Rated breaking capacity	30 kA	Version	Fuse cartridge

### General

Installation advice	Direct mounting
---------------------	-----------------

### Rating data

Rated voltage	1,000
---------------	-------

### Classifications

ETIM 6.0	EC002936	ETIM 7.0	EC002936
ETIM 8.0	EC002936	ECLASS 9.0	27-14-20-90
ECLASS 9.1	27-14-20-90	ECLASS 10.0	27-14-20-90
ECLASS 11.0	27-14-20-90	ECLASS 12.0	27-14-20-90

### Approvals

ROHS	Conform
------	---------

## FUSE 1KV DC 10A 10/38

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

## Technical data

[www.weidmueller.com](http://www.weidmueller.com)

### Downloads

User Documentation [StorageConditionsTerminalBlocks](#)

Catalogues [Catalogues in PDF-format](#)

Brochures